

**CBC-SP 2-12/50 BK****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Similar to illustration**

Spiral and webbing hoses are particularly suitable for the construction of space-saving cable routing systems in switch gears and control cabinets. They are used for guiding, protecting and bundling cables and wires - for example, in the transition between the enclosure interior and the door.

**General ordering data**

Version	Protective cable hose coil
Order No.	<a href="#">2588590000</a>
Type	CBC-SP 2-12/50 BK
GTIN (EAN)	4050118602586
Qty.	50 m

**CBC-SP 2-12/50 BK****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Length	400,000 mm	Length (inches)	15,748 inch
Diameter	3 mm	Net weight	5.56 g

**Temperatures**

Operating temperature range	-15...60 °C
-----------------------------	-------------

**General information**

Bundle diameter, max.	12 mm	Bundle diameter, min.	2 mm
Colour	black, RAL 7021	Diameter	3 mm
Material	Polyethylene	Nominal diameter	1.5 mm
Operating temperature range	-15...60 °C	Usable cross-section	113 mm <sup>2</sup>

**Classifications**

ETIM 6.0	EC001182	ETIM 7.0	EC001182
ETIM 8.0	EC001182	ETIM 9.0	EC001182
ECLASS 9.1	27-43-03-03	ECLASS 10.0	27-43-03-03
ECLASS 11.0	27-43-03-03	ECLASS 12.0	27-43-03-03
ECLASS 13.0	27-43-03-03		

**Environmental Product Compliance**

REACH SVHC	/
------------	---

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--