

**CD-LID 100 LTGY****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Similar to illustration**

DIN EN 4545-2



Increase your wiring flexibility with our comprehensive range of accessories available from a single source.

**General ordering data**

Version	Cable duct cover, 100 mm
Order No.	<a href="#">2589140000</a>
Type	CD-LID 100 LTGY
GTIN (EAN)	4050118602562
Qty.	2 m

**CD-LID 100 LTGY****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Width	100 mm	Width (inches)	3.937 inch
Length	2,000 mm	Length (inches)	78.74 inch
Net weight	214 g		

**Temperatures**

Operating temperature range	-25...105 °C
-----------------------------	--------------

**General information**

Colour	Light Grey	Flexible wiring duct	No
Halogen	No	Lid	Yes
Material	PC-ABS	Non-tracking	Yes
Operating temperature range	-25...105 °C	Type of mounting	Snap-on
UL 94 flammability rating	V-0		

**Classifications**

ETIM 6.0	EC000727	ETIM 7.0	EC000727
ETIM 8.0	EC000727	ETIM 9.0	EC000727
ECLASS 9.1	27-40-07-76	ECLASS 10.0	27-40-07-76
ECLASS 11.0	27-40-07-76	ECLASS 12.0	27-40-07-76
ECLASS 13.0	27-40-07-76		

**Environmental Product Compliance**

REACH SVHC	/
------------	---

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--