

CD-LID 100 LTGY**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

Increase your wiring flexibility with our comprehensive range of accessories available from a single source.

General ordering data

| | |
|------------|----------------------------|
| Version | Cable duct cover, 100 mm |
| Order No. | 2589140000 |
| Type | CD-LID 100 LTGY |
| GTIN (EAN) | 4050118602562 |
| Qty. | 2 m |

CD-LID 100 LTGY**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

| | | | |
|------------|----------|-----------------|------------|
| Width | 100 mm | Width (inches) | 3.937 inch |
| Length | 2,000 mm | Length (inches) | 78.74 inch |
| Net weight | 214 g | | |

Temperatures

| | |
|-----------------------------|--------------|
| Operating temperature range | -25...105 °C |
|-----------------------------|--------------|

General information

| | | | |
|-----------------------------|--------------|----------------------|---------|
| Colour | Light Grey | Flexible wiring duct | No |
| Halogen | No | Lid | Yes |
| Material | PC-ABS | Non-tracking | Yes |
| Operating temperature range | -25...105 °C | Type of mounting | Snap-on |
| UL 94 flammability rating | V-0 | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000727 | ETIM 7.0 | EC000727 |
| ETIM 8.0 | EC000727 | ETIM 9.0 | EC000727 |
| ECLASS 9.1 | 27-40-07-76 | ECLASS 10.0 | 27-40-07-76 |
| ECLASS 11.0 | 27-40-07-76 | ECLASS 12.0 | 27-40-07-76 |
| ECLASS 13.0 | 27-40-07-76 | | |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------|------------------------------------------|
| Catalogues | Catalogues in PDF-format |
|------------|------------------------------------------|