

CD-LID 75 LTGY**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

Increase your wiring flexibility with our comprehensive range of accessories available from a single source.

General ordering data

Version	Cable duct cover, 75 mm
Order No.	2589170000
Type	CD-LID 75 LTGY
GTIN (EAN)	4050118602609
Qty.	2 m

CD-LID 75 LTGY**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Width	75 mm	Width (inches)	2.953 inch
Length	2,000 mm	Length (inches)	78.74 inch
Net weight	105 g		

Temperatures

Operating temperature range	-25...105 °C
-----------------------------	--------------

General information

Colour	Light Grey	Flexible wiring duct	No
Halogen	No	Lid	Yes
Material	PC-ABS	Non-tracking	Yes
Operating temperature range	-25...105 °C	Type of mounting	Snap-on
UL 94 flammability rating	V-0		

Classifications

ETIM 6.0	EC000727	ETIM 7.0	EC000727
ETIM 8.0	EC000727	ETIM 9.0	EC000727
ECLASS 9.1	27-40-07-76	ECLASS 10.0	27-40-07-76
ECLASS 11.0	27-40-07-76	ECLASS 12.0	27-40-07-76
ECLASS 13.0	27-40-07-76		

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--