

CBC 25/20 BK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

Spiral and webbing hoses are particularly suitable for the construction of space-saving cable routing systems in switch gears and control cabinets. They are used for guiding, protecting and bundling cables and wires - for example, in the transition between the enclosure interior and the door.

General ordering data

Version	Protective cable hose
Order No.	2589430000
Type	CBC 25/20 BK
GTIN (EAN)	4050118603606
Qty.	20 m

CBC 25/20 BK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Length	20,000 mm	Length (inches)	787.4 inch
Diameter	25 mm	Net weight	95.2 g

Temperatures

Operating temperature range	-20...90 °C
-----------------------------	-------------

General information

Bundle diameter, max.	25 mm	Colour	black, RAL 7021
Diameter	25 mm	Material	Polypropylene
Nominal diameter	25 mm	Operating temperature range	-20...90 °C
UL 94 flammability rating	HB	Usable cross-section	490 mm ²

Classifications

ETIM 6.0	EC002604	ETIM 7.0	EC002604
ETIM 8.0	EC002604	ETIM 9.0	EC002604
ECLASS 9.1	27-43-03-02	ECLASS 10.0	27-43-03-02
ECLASS 11.0	27-43-03-02	ECLASS 12.0	27-43-03-02
ECLASS 13.0	27-43-03-02		

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--