

CD 25X25 5/7.5 GY**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

The broad range of cable ducts offers you a flexible wire management system in a constant quality. The accurately sizes of the punched holes in accordance to DIN EN 50085-2-3 enables you a precise installation. Next to wire holding lugs as fixing aid for already installed wires, the optimal closing mechanism provide an easy snapping as well as a safe fit of the lid.

General ordering data

Version	Cable duct, 25 mm x 25 mm, 5.00 mm x 7.50 mm, 2000 mm
Order No.	2589520000
Type	CD 25X25 5/7.5 GY
GTIN (EAN)	4050118601237
Qty.	84 m

CD 25X25 5/7.5 GY

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Height	25 mm	Height (inches)	0.984 inch
Width	25 mm	Width (inches)	0.984 inch
Length	2,000 mm	Length (inches)	78.74 inch
Net weight	166.571 g		

Temperatures

Operating temperature range	-5...60 °C
-----------------------------	------------

General information

Colour	grey	Flexible wiring duct	No
Halogen	Yes	Included in delivery	Cable duct, Lid
Lid	Yes	Material	PVC / lead-free
Non-tracking	Yes	Operating temperature range	-5...60 °C
Slit gap	7.5 mm	Slit width	5 mm
Standards	In accordance with DIN EN 50085	Type of mounting	when screwed in, With adhesive, Riveted
UL 94 flammability rating	V-0	Usable cross-section	440 mm²
Version of side panel	slotted		

Classifications

ETIM 6.0	EC000012	ETIM 7.0	EC000012
ETIM 8.0	EC000012	ETIM 9.0	EC000012
ECLASS 9.1	27-40-07-03	ECLASS 10.0	27-40-07-03
ECLASS 11.0	27-40-07-03	ECLASS 12.0	27-40-07-03
ECLASS 13.0	27-40-07-03	ECLASS 14.0	27-40-07-03

Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E500004

Downloads

Catalogues	Catalogues in PDF-format
------------	--

CD 25X25 5/7.5 GY

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings



CD 25X25 5/7.5 GY

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Marking



Increase your wiring flexibility with our comprehensive range of accessories available from a single source.

General ordering data

Type	CD-LB	Version
Order No.	2562680000	Cable duct tag rail, 15 mm x
GTIN (EAN)	4050118571646	
Qty.	150 pc(s).	
Type	CD-LBK	Version
Order No.	2554120000	Cable duct tag rail kit, 30 mm x
GTIN (EAN)	4050118564242	
Qty.	20 pc(s).	
Type	CD-LBH	Version
Order No.	2562850000	Cable duct tag rail holder, 30 mm x
GTIN (EAN)	4050118571691	
Qty.	150 pc(s).	

Rivet and cover

Increase your wiring flexibility with our comprehensive range of accessories available from a single source.



General ordering data

Type	EXRV 4.5	Version
Order No.	2562700000	Expanding rivet, 27.5 mm x
GTIN (EAN)	4050118571622	
Qty.	1,000 pc(s).	
Type	EXRV 6.5	Version
Order No.	2562690000	Expanding rivet, 32 mm x
GTIN (EAN)	4050118571639	
Qty.	1,000 pc(s).	
Type	EXRV-T 6.5	Version
Order No.	2562710000	Expanding-rivet tool
GTIN (EAN)	4050118571615	
Qty.	4 pc(s).	

CD 25X25 5/7.5 GY**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories**

Type	EXRV-T 4.5	Version
Order No.	2562720000	Expanding-rivet tool
GTIN (EAN)	4050118571578	
Qty.	4 pc(s).	

Side arm

Increase your wiring flexibility with our comprehensive range of accessories available from a single source.

**General ordering data**

Type	CD-RETA	Version
Order No.	2554080000	Cable duct binder arm
GTIN (EAN)	4050118564204	
Qty.	100 pc(s).	

DIN

Increase your wiring flexibility with our comprehensive range of accessories available from a single source.

**General ordering data**

Type	CD-LID 25 GY	Version
Order No.	2590110000	Cable duct cover, 25 mm
GTIN (EAN)	4050118600650	
Qty.	2 m	