

**THM MULTIMARK****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

**General ordering data**

|            |   |
|------------|---|
| Version    | Marking systems, Thermotransfer printer, Thermal transfer, 300 DPI, MultiMark, Shrink-fit sleeves, Label reel |
| Order No.  | <a href="#">2599430000</a>  |
| Type       | THM MULTIMARK   |
| GTIN (EAN) | 4050118626377   |
| Qty.       | 1 pc(s).  |

## THM MULTIMARK

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |         |                 |             |
|------------|---------|-----------------|-------------|
| Depth      | 253 mm  | Depth (inches)  | 9.961 inch  |
| Height     | 320 mm  | Height (inches) | 12.598 inch |
| Width      | 253 mm  | Width (inches)  | 9.961 inch  |
| Net weight | 5,800 g |                 |             |

## Labelling systems

|                        |   |                                       |                   |
|------------------------|---|---------------------------------------|-------------------|
| Included in delivery   | THM MultiMark, Manual, USB cable, Mains cable, Euro plug, US plug, UK plug, Printer driver, Software M-Print® PRO, RIBBON MM-TB 25/360 SW ink ribbon, RIBBON MM 110/360 SW ink ribbon, Ink ribbon core, Print roller, Pressure roller | Interface                             | USB 2.0, Ethernet |
| Marker type            | MultiMark, Shrink-fit sleeves, Label reel   | Memory (RAM)                          | 256 MB            |
| Operating system       | Windows 7, Windows 8, Windows 8.1, Windows 10   | Operation with rechargeable batteries | No                |
| Print resolution, max. | 300 DPI   | Printing method                       | Thermal transfer  |
| Printing speed         | max. 150 mm/s   | Software                              | M-Print® PRO      |
| System requirements    | PC with operating system Windows 7, 8 or 10   | Voltage supply                        | 100...240 V AC    |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000610    | ETIM 7.0    | EC000610    |
| ETIM 8.0    | EC000610    | ETIM 9.0    | EC000610    |
| ECLASS 9.0  | 24-32-11-90 | ECLASS 9.1  | 24-32-11-02 |
| ECLASS 10.0 | 24-32-11-90 | ECLASS 11.0 | 24-32-11-90 |
| ECLASS 12.0 | 24-32-11-90 | ECLASS 13.0 | 24-32-11-90 |

## Environmental Product Compliance

|            |                                      |
|------------|--------------------------------------|
| REACH SVHC | Lead 7439-92-1                       |
| SCIP       | 7d9d08e1-8ede-49b5-a637-5ea27a383bef |

## Approvals

Approvals



ROHS Conform

## Downloads

|   |   |
|---|---|
| Approval/Certificate/Document of Conformity | <a href="#">China RoHS Declaration</a><br><a href="#">Declaration of Conformity</a> |
| User Documentation                          | <a href="#">THM MULTIMARK</a>   |
| Catalogues                                  | <a href="#">Catalogues in PDF-format</a>  |