

CMA-RCM-DACT-35**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration****Difference current transformer** (Residual current monitoring, RCM)

This type is specialised in the detection of residual currents in 3 / 4-wire AC networks.

Its special features are:

Highly sensitive current sensor for the detection of even the smallest residual currents, fixed switching hysteresis of 5%, high safety thanks to integrated overvoltage protection and coverage of a wide frequency range.

General ordering data

Version	Residual current transformer, Primary current: 25 A, Round conductor: 35.00 mm, closed current transformer
Order No.	2603430000
Type	CMA-RCM-DACT-35
GTIN (EAN)	4050118665413
Qty.	1 pc(s).
Manufacturer	MBS AG

CMA-RCM-DACT-35

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	30 mm	Depth (inches)	1.181 inch
Height	86.5 mm	Height (inches)	3.406 inch
Width	104 mm	Width (inches)	4.094 inch
Net weight	240 g		

Temperatures

Storage temperature	-25 °C...70 °C	Operating temperature	-10 °C...70 °C
---------------------	----------------	-----------------------	----------------

Measuring current input

Residual current measuring	Yes
----------------------------	-----

Dimensions of live conductors

Type of conductor	Insulated conductor only	Round conductor	35 mm
Installation location	Indoor use		

Electrical attributes

Frequency band	30 Hz...3 kHz	Load	0 VA
Primary current	25 A	Secondary current	0...0.04 A
Tolerance class	1	Transmission ratio	1:600

Technical properties

Coil resistance	8 Ω	Measurement accuracy	Class 1 (IEC 6206-21)
Protection degree	IP40		

Input

Input measurement range	0.02...2 A / 0.25...25 A depending on terminal as- signment
-------------------------	---

Insulation coordination

Galvanic isolation	yes	Impulse withstand voltage	8 kV
Pollution severity	3	Rated voltage	800 V
Standard	EN 60044/1	Tolerance class	1

Classifications

ETIM 6.0	EC002048	ETIM 7.0	EC002048
ETIM 8.0	EC002048	ETIM 9.0	EC002048
ECLASS 9.0	27-21-09-02	ECLASS 9.1	27-21-09-02
ECLASS 10.0	27-21-09-02	ECLASS 11.0	27-21-09-02
ECLASS 12.0	27-21-09-02	ECLASS 13.0	27-21-09-02
ECLASS 14.0	27-21-09-02		

Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant

CMA-RCM-DACT-35

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Con-	
formity	Declaration of Conformity

User Documentation	Device description – Instruction sheet
--------------------	--

Catalogues	Catalogues in PDF-format
------------	--

CMA-RCM-DACT-35

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Dimensional drawing

