

SQV 3/10**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

General ordering data

Version	Cross-connector (terminal), when screwed in, Number of poles: 10, Pitch in mm (P): 9.00, Insulated: No, 41 A, black, grey
Order No.	2615070000
Type	SQV 3/10
GTIN (EAN)	4050118653915
Qty.	10 pc(s).

SQV 3/10

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	22.7 mm	Depth (inches)	0.894 inch
Height	4.3 mm	Height (inches)	0.169 inch
Width	95 mm	Width (inches)	3.74 inch
Net weight	2.44 g		

Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

Material data

Material	PA	Colour	black, grey
----------	----	--------	-------------

System specifications

Version	Cross-connector
---------	-----------------

Additional technical data

Explosion-tested version	No	Type of fixing	when screwed in
Type of mounting	when screwed in		

Cross-connector

Rated current, multi-pole	41 A	Type	Cross-connector
---------------------------	------	------	-----------------

Dimensions

Pitch in mm (P)	9 mm
-----------------	------

General

Number of poles	10
-----------------	----

Rating data

Rated current	41 A
---------------	------

Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ECLASS 9.0	27-14-11-40	ECLASS 9.1	27-14-11-40
ECLASS 10.0	27-14-11-40	ECLASS 11.0	27-14-11-40
ECLASS 12.0	27-14-11-40	ECLASS 13.0	27-25-03-03

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format

Creation date May 23, 2024 2:56:21 PM CEST