

SQV 3/10**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

General ordering data

| | |
|------------|---|
| Version | Cross-connector (terminal), when screwed in, black, grey, 41 A, Number of poles: 10, Pitch in mm (P): 9.00, Insulated: No, Width: 95 mm |
| Order No. | 2615070000 |
| Type | SQV 3/10 |
| GTIN (EAN) | 4050118653915 |
| Qty. | 10 pc(s). |

SQV 3/10**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

| | | | |
|------------|---------|-----------------|------------|
| Depth | 22.7 mm | Depth (inches) | 0.894 inch |
| Height | 4.3 mm | Height (inches) | 0.169 inch |
| Width | 95 mm | Width (inches) | 3.74 inch |
| Net weight | 2.44 g | | |

Temperatures

| | |
|---------------------|----------------|
| Storage temperature | -25 °C...55 °C |
|---------------------|----------------|

Material data

| | | | |
|----------|----|--------|-------------|
| Material | PA | Colour | black, grey |
|----------|----|--------|-------------|

System specifications

| | |
|---------|-----------------|
| Version | Cross-connector |
|---------|-----------------|

Additional technical data

| | | | |
|--------------------------|-----------------|----------------|-----------------|
| Explosion-tested version | No | Type of fixing | when screwed in |
| Type of mounting | when screwed in | | |

Cross-connector

| | | | |
|---------------------------|------|------|-----------------|
| Rated current, multi-pole | 41 A | Type | Cross-connector |
|---------------------------|------|------|-----------------|

Dimensions

| | |
|-----------------|------|
| Pitch in mm (P) | 9 mm |
|-----------------|------|

General

| | |
|-----------------|----|
| Number of poles | 10 |
|-----------------|----|

Rating data

| | |
|---------------|------|
| Rated current | 41 A |
|---------------|------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000489 | ETIM 7.0 | EC000489 |
| ETIM 8.0 | EC000489 | ETIM 9.0 | EC000489 |
| ECLASS 9.0 | 27-14-11-40 | ECLASS 9.1 | 27-14-11-40 |
| ECLASS 10.0 | 27-14-11-40 | ECLASS 11.0 | 27-14-11-40 |
| ECLASS 12.0 | 27-14-11-40 | ECLASS 13.0 | 27-25-03-03 |
| ECLASS 14.0 | 27-25-03-03 | | |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| REACH SVHC | / |
| RoHS Compliance Status | Compliant without exemption |

SQV 3/10

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------------|--|
| Engineering Data | CAD data – STEP |
| Catalogues | Catalogues in PDF-format |