

**SQV 6/4****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Screwable cross-connections are easy to mount and de-mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

**General ordering data**

Version	Cross-connector (terminal), when screwed in, Number of poles: 4, Pitch in mm (P): 18.00, Insulated: No, 125 A, black, grey
Order No.	<a href="#">2615100000</a>
Type	SQV 6/4
GTIN (EAN)	4050118653885
Qty.	50 pc(s).

## SQV 6/4

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	32 mm	Depth (inches)	1.26 inch
Height	7.5 mm	Height (inches)	0.295 inch
Width	61.1 mm	Width (inches)	2.406 inch
Net weight	17.42 g		

## Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

## Material data

Material	PA	Colour	black, grey
----------	----	--------	-------------

## System specifications

Version	Cross-connector
---------	-----------------

## Additional technical data

Explosion-tested version	No	Type of fixing	when screwed in
Type of mounting	when screwed in		

## Cross-connector

Rated current, multi-pole	125 A	Type	Cross-connector
---------------------------	-------	------	-----------------

## Dimensions

Pitch in mm (P)	18 mm
-----------------	-------

## General

Number of poles	4
-----------------	---

## Rating data

Rated current	125 A
---------------	-------

## Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ECLASS 9.0	27-14-11-40	ECLASS 9.1	27-14-11-40
ECLASS 10.0	27-14-11-40	ECLASS 11.0	27-14-11-40
ECLASS 12.0	27-14-11-40	ECLASS 13.0	27-25-03-03

## Approvals

ROHS	Conform
------	---------

## Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>