

**SM-FO 27/12.5 MM WS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Prevention of incorrect operation: SM**

MultiMark device markers can be used with marking materials from different manufacturers. Wherever they are used, they ensure that all components, such as control and signalling devices from different vendors, are clearly assigned.

**Your benefits with MultiMark**

- "Different materials for various requirements"
- Can be used with equipment from many manufacturers
- Device markers with a familiar design

**General ordering data**

|                    |   |
|--------------------|---|
| Version            | SwitchMark, Device markers, 12.5 x 27 mm, white       |
| Order No.          | <a href="#">2621220000</a>                            |
| Type               | SM-FO 27/12.5 MM WS                                   |
| GTIN (EAN)         | 4050118625820   |
| Qty.               | 500 pc(s).  |
| compatible printer | <a href="#">2599430000</a> <a href="#">2599440000</a> |

**SM-FO 27/12.5 MM WS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 0.55 mm | Depth (inches)  | 0.022 inch |
| Height     | 12.5 mm | Height (inches) | 0.492 inch |
| Width      | 27 mm   | Width (inches)  | 1.063 inch |
| Net weight | 0.1 g   |                 |            |

**Temperatures**

|                             |             |
|-----------------------------|-------------|
| Operating temperature range | -30...80 °C |
|-----------------------------|-------------|

**General data**

|                                   |                               |                                   |                             |
|-----------------------------------|-------------------------------|-----------------------------------|-----------------------------|
| Adhesive                          | PE-foam with acrylic adhesive | Approval acc. to UL 969           | Yes                         |
| Colour                            | white                         | Halogen                           | No                          |
| Material                          | Polyester                     | Number per roll                   | 500                         |
| Operating temperature range       | -30...80 °C                   | Operating temperature range, max. | 80 °C                       |
| Operating temperature range, min. | -30 °C                        | Size of labelling field           | 12.5 x 27 mm                |
| UL 94 flammability rating         | V-0                           | Version                           | halogen-free, Self-adhesive |
| Width                             | 27 mm                         |                                   |                             |

**Device markers**

|         |    |
|---------|----|
| Halogen | No |
|---------|----|

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001288    | ETIM 7.0    | EC001288    |
| ETIM 8.0    | EC001288    | ETIM 9.0    | EC001288    |
| ECLASS 9.0  | 27-40-06-29 | ECLASS 9.1  | 27-40-06-29 |
| ECLASS 10.0 | 27-40-06-29 | ECLASS 11.0 | 27-28-11-04 |
| ECLASS 12.0 | 27-28-11-04 | ECLASS 13.0 | 27-28-11-04 |
| ECLASS 14.0 | 27-28-11-04 |             |             |

**Environmental Product Compliance**

|                        |                             |
|------------------------|-----------------------------|
| REACH SVHC             | /                           |
| RoHS Compliance Status | Compliant without exemption |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|            |  |
|------------|--|
| Catalogues | <a href="#">Catalogues in PDF-format</a> |
|------------|--|

### SM-FO 27/12.5 MM WS

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings



**SM-FO 27/12.5 MM WS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Ink ribbons**

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

**General ordering data**

|            |                            |            |
|------------|----------------------------|------------|
| Type       | RIBBON MM 76/360 SW        | Version    |
| Order No.  | <a href="#">2005080000</a> | Ink ribbon |
| GTIN (EAN) | 4050118389951              |            |
| Qty.       | 1 pc(s).                   |            |

**THM MULTIMARK PLUS**

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

**General ordering data**

|            |                            |
|------------|----------------------------|
| Type       | MM PLUS ROLLER 110         |
| Order No.  | <a href="#">2672590000</a> |
| GTIN (EAN) | 4050118708097              |
| Qty.       | 1 pc(s).                   |

**SM-FO 27/12.5 MM WS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****THM MULTIMARK**

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

**General ordering data**

|            |                            |
|------------|----------------------------|
| Type       | THM MMP ROLLER 115         |
| Order No.  | <a href="#">1357420000</a> |
| GTIN (EAN) | 4050118160314              |
| Qty.       | 1 pc(s).                   |