

THM WO 25/37 WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality thermal transfer printers

General ordering data

Version	THM, Conductor and cable markers, 4.8 - 7 mm, 25 x 37 mm, white
Order No.	2621510000
Type	THM WO 25/37 WS
GTIN (EAN)	4050118625530
Qty.	2,500 pc(s).
compatible printer	2599430000 2599440000

THM WO 25/37 WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	0.025 mm	Depth (inches)	0.001 inch
Height	25 mm	Height (inches)	0.984 inch
Width	37 mm	Width (inches)	1.457 inch
Net weight	0.16 g		

Temperatures

Operating temperature range	-40...
-----------------------------	--------

General data

Colour	white	
Number of markers per combination	1 Label reel = Conductor and cable markers	
Number of markers per packaging unit	Form of supply	Label reel
Number per roll	2,500	
Operating temperature range	-40...	
Operating temperature range, min.	-40 °C	
Size of labelling field	15 x 25 mm	
Type of printing	neutral	
UL 94 flammability rating	V-0	
Width	37 mm	

Conductor and cable markers

Conductor O.D.	4.8 - 7 mm	Conductor O.D., max.	7 mm
Conductor O.D., min.	4.8 mm		

Classifications

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ETIM 9.0	EC001288
ECLASS 9.0	27-40-06-29	ECLASS 9.1	27-40-06-29
ECLASS 10.0	27-40-06-29	ECLASS 11.0	27-28-11-04
ECLASS 12.0	27-28-11-04	ECLASS 13.0	27-28-11-04

Environmental Product Compliance


REACH SVHC	/
------------	---

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--



THM WO 25/37 WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Ink ribbons**

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	RIBBON MM 110/360 SW	Version
Order No.	2005070000	Ink ribbon
GTIN (EAN)	4050118390049	
Qty.	1 pc(s).	