

**THM WO 14/22 WS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality thermal transfer printers

**General ordering data**

Version	THM, Conductor and cable markers, 1.9 - 5 mm, 14 x 22 mm, white
Order No.	<a href="#">2621530000</a>
Type	THM WO 14/22 WS
GTIN (EAN)	4050118625516
Qty.	5,000 pc(s).
compatible printer	<a href="#">2599430000</a> <a href="#">2599440000</a>

**Technical data****Dimensions and weights**

Depth	0.025 mm	Depth (inches)	0.001 inch
Height	14 mm	Height (inches)	0.551 inch
Width	22 mm	Width (inches)	0.866 inch
Net weight	0.05 g		

**Temperatures**

Operating temperature range	-40...
-----------------------------	--------

**General data**

Colour	white	
Number of markers per combination	1 Label reel = Conductor and cable markers	
Number of markers per packaging unit	Form of supply	Label reel
Number per roll	5,000	
Operating temperature range	-40...	
Operating temperature range, min.	-40 °C	
Size of labelling field	6 x 14 mm	
Type of printing	neutral	
UL 94 flammability rating	V-0	
Width	22 mm	

**Conductor and cable markers**

Conductor O.D.	1.9 - 5 mm	Conductor O.D., max.	5 mm
Conductor O.D., min.	1.9 mm		

**Classifications**

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ETIM 9.0	EC001288
ECLASS 9.0	27-40-06-29	ECLASS 9.1	27-40-06-29
ECLASS 10.0	27-40-06-29	ECLASS 11.0	27-28-11-04
ECLASS 12.0	27-28-11-04	ECLASS 13.0	27-28-11-04

**Environmental Product Compliance**

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--

