


**HS-FR 1.2-2.4/25 MM Y****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

**General ordering data**

Version	Conductor and cable markers, 1.2 - 2.4 mm, 24.9 x 4 mm, yellow
Order No.	<a href="#">2621570000</a>
Type	HS-FR 1.2-2.4/25 MM Y
GTIN (EAN)	4050118625479
Qty.	2,000 pc(s).
compatible printer	<a href="#">2599430000</a> <a href="#">2599440000</a>

## HS-FR 1.2-2.4/25 MM Y

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Dimensions and weights

Depth	0.77 mm	Depth (inches)	0.03 inch
Height	24.9 mm	Height (inches)	0.98 inch
Width	4 mm	Width (inches)	0.157 inch
Net weight	0.252 g		

### Temperatures

Operating temperature range	-55...125 °C
-----------------------------	--------------

### General data

Colour	yellow	Halogen	No
Material	Polyolefine	Operating temperature range	-55...125 °C
Operating temperature range, max.	125 °C	Operating temperature range, min.	-55 °C
Size of labelling field	4 x 24.9 mm	Width	4 mm

### Conductor and cable markers

Conductor O.D.	1.2 - 2.4 mm	Conductor O.D., max.	2.4 mm
Conductor O.D., min.	1.2 mm	Conductor cross-section, max.	0.5 mm <sup>2</sup>
Conductor cross-section, min.	0.25 mm <sup>2</sup>	Cross-section for connected wire	0.25 - 0.5 mm <sup>2</sup>
Halogen	No	Rate of shrinkage	2:1
Recommended shrinking temperature	90 °C	Wire connection cross section AWG, max.	AWG 20
Wire connection cross section AWG, min.	AWG 24		

### Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ECLASS 9.0	27-40-04-01	ECLASS 9.1	27-40-04-01
ECLASS 10.0	27-40-04-01	ECLASS 11.0	27-28-11-02
ECLASS 12.0	27-28-11-02	ECLASS 13.0	27-28-11-02
ECLASS 14.0	27-28-11-02		

### Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

### Approvals

ROHS	Conform
------	---------

### Downloads

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--

### HS-FR 1.2-2.4/25 MM Y

**Weidmüller Interface GmbH & Co. KG**


Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings



**HS-FR 1.2-2.4/25 MM Y****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Ink ribbons**

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

**General ordering data**

Type	RIBBON MM-HS 60/300 SW	Version
Order No.	<a href="#">2448880000</a>	Ink ribbon
GTIN (EAN)	4050118462944	
Qty.	1 pc(s).	

**THM MULTIMARK**

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

**General ordering data**

Type	THM MMP ROLLER 115
Order No.	<a href="#">1357420000</a>
GTIN (EAN)	4050118160314
Qty.	1 pc(s).

### HS-FR 1.2-2.4/25 MM Y

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

### THM MULTIMARK PLUS



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

### General ordering data

Type	MM PLUS ROLLER 110
Order No.	<a href="#">2672590000</a>
GTIN (EAN)	4050118708097
Qty.	1 pc(s).