

AAM 35-185 YE FLASH**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Power feed-in**

Our wide range of W-Series terminal blocks with our WPD main line branch terminals, which are optimised to guarantee both convenience and space gains, ensures a secure and convenient connection at the power feed-in.

General ordering data

Version	Terminal marker, 23.5 x 12 mm, Pitch in mm (P): 12.00 yellow
Order No.	2635600000
Type	AAM 35-185 YE FLASH
GTIN (EAN)	4050118674545
Qty.	40 pc(s).

AAM 35-185 YE FLASH**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	6.8 mm	Depth (inches)	0.268 inch
Height	23.5 mm	Height (inches)	0.925 inch
Width	12 mm	Width (inches)	0.472 inch
Net weight	0.425 g		

Temperatures

Operating temperature range	-40...100 °C
-----------------------------	--------------

Material data

Material	PA 6.6	Colour	yellow
UL 94 flammability rating	V-2		

Rating data IECEx/ATEX

Operating temperature range	-40...100 °C
-----------------------------	--------------

Dimensions

Pitch in mm (P)	12 mm
-----------------	-------

General

Operating temperature range, max.	100 °C	Operating temperature range, min.	-40 °C
-----------------------------------	--------	-----------------------------------	--------

Classifications

ETIM 6.0	EC000761	ETIM 7.0	EC000761
ETIM 8.0	EC000761	ETIM 9.0	EC000761
ECLASS 9.0	27-14-11-37	ECLASS 9.1	27-14-11-37
ECLASS 10.0	27-14-11-37	ECLASS 11.0	27-28-11-01
ECLASS 12.0	27-28-11-01	ECLASS 13.0	27-28-11-01

Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format

AAM 35-185 YE FLASH

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

