

CABTITE BP 20MM PA**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

Similar to illustration

The blanking plugs are used for the safe closing of un-needed cable passages in the sealing elements.

General ordering data

Version	Blind plug, Cabtite (cable entry system), Polyamide, red, Height: 22 mm, Width: 20 mm, Depth: 22 mm, -60 °C...100 °C, IP66
Order No.	2652440000
Type	CABTITE BP 20MM PA
GTIN (EAN)	4050118662542
Qty.	25 pc(s).

CABTITE BP 20MM PA**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	22 mm	Depth (inches)	0.866 inch
Height	22 mm	Height (inches)	0.866 inch
Width	20 mm	Width (inches)	0.787 inch
Length	22 mm	Length (inches)	0.866 inch
Diameter	20 mm	Net weight	1.1 g

Temperatures

Operating temperature	-60 °C... 100 °C
-----------------------	------------------

General information

Halogen	No	Material	Polyamide
Outer cable diameter, max.	20 mm	Outer cable diameter, min.	20 mm
Protection degree	IP66	UL 94 flammability rating	V-0

Classifications

ETIM 6.0	EC000879	ETIM 7.0	EC000879
ETIM 8.0	EC000879	ETIM 9.0	EC000879
ECLASS 9.0	27-14-44-21	ECLASS 9.1	27-14-44-21
ECLASS 10.0	27-14-44-21	ECLASS 11.0	27-14-44-21
ECLASS 12.0	27-14-08-07	ECLASS 13.0	27-14-08-07
ECLASS 14.0	27-14-08-07		

Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
User Documentation	Cabtite Installation Instructions
Catalogues	Catalogues in PDF-format