

**CABTITE BP 25MM PA****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Similar to illustration**

Similar to illustration

The blanking plugs are used for the safe closing of un-needed cable passages in the sealing elements.

**General ordering data**

Version	Blind plug, Cabtite (cable entry system), Polyamide, red, Height: 30 mm, Width: 25 mm, Depth: 30 mm, -60 °C...100 °C, IP66
Order No.	<a href="#">2652460000</a>
Type	CABTITE BP 25MM PA
GTIN (EAN)	4050118662566
Qty.	50 pc(s).

**CABTITE BP 25MM PA****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	30 mm	Depth (inches)	1.181 inch
Height	30 mm	Height (inches)	1.181 inch
Width	25 mm	Width (inches)	0.984 inch
Length	30 mm	Length (inches)	1.181 inch
Diameter	25 mm	Net weight	2.1 g

**Temperatures**

Operating temperature	-60 °C... 100 °C
-----------------------	------------------

**General information**

Halogen	No	Material	Polyamide
Outer cable diameter, max.	25 mm	Outer cable diameter, min.	25 mm
Protection degree	IP66	UL 94 flammability rating	V-0

**Classifications**

ETIM 6.0	EC000879	ETIM 7.0	EC000879
ETIM 8.0	EC000879	ETIM 9.0	EC000879
ECLASS 9.0	27-14-44-21	ECLASS 9.1	27-14-44-21
ECLASS 10.0	27-14-44-21	ECLASS 11.0	27-14-44-21
ECLASS 12.0	27-14-08-07	ECLASS 13.0	27-14-08-07

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">Cabtite Installation Instructions</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>