


KCMA-RCM-58D**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Difference current transformer** (Residual current monitoring, RCM)

This type is specialised in the detection of residual currents in 3 / 4-wire AC networks.

Its special features are:

Highly sensitive current sensor for the detection of even the smallest residual currents, fixed switching hysteresis of 5%, high safety thanks to integrated overvoltage protection and coverage of a wide frequency range.

General ordering data

Version	Residual current transformer (RCM), Primary current: 18 A, Round conductor: 50.00 mm, Split-core current transformer
Order No.	2656280000
Type	KCMA-RCM-58D
GTIN (EAN)	4050118666359
Qty.	1 pc(s).
Manufacturer	MBS AG

KCMA-RCM-58D

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	158 mm	Depth (inches)	6.22 inch
Width	58 mm	Width (inches)	2.283 inch
Length	125 mm	Length (inches)	4.921 inch
Net weight	240 g		

Temperatures

Operating temperature	-5 °C...45 °C
-----------------------	---------------

Measuring current input

Residual current measuring	Yes
----------------------------	-----

Dimensions of live conductors

Type of conductor	Insulated conductor only	Round conductor	50 mm
Rail	50 x 80 mm	Installation location	Indoor use

Electrical attributes

Frequency band	30...1000 Hz	Primary conductor temperature	70 °C
Primary current	18 A	Secondary current	0...0.04 A
Tolerance class	1	Transmission ratio	1:600

Technical properties

Insulation class	E	Nominal frequency	50 Hz
Protection degree	IP20	Thermal rated continuous current I_{thermal}	$60 \times I_{\text{rated}}$ for 1 second

Insulation coordination

Standard	EN 60044/1	Tolerance class	1
----------	------------	-----------------	---

Classifications

ETIM 6.0	EC002048	ETIM 7.0	EC002048
ETIM 8.0	EC002048	ETIM 9.0	EC002048
ECLASS 9.0	27-21-09-02	ECLASS 9.1	27-21-09-02
ECLASS 10.0	27-21-09-02	ECLASS 11.0	27-21-09-02
ECLASS 12.0	27-21-09-02	ECLASS 13.0	27-21-09-02

Approvals

ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	EU Declaration of Conformity
User Documentation	Device description – Instruction sheet english
Catalogues	Catalogues in PDF-format

KCMA-RCM-58D

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Dimensional drawing

