


THM WO VIN 25.4/38.1 WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality thermal transfer printers

General ordering data

Version	THM, Conductor and cable markers, 4 - 8 mm, 25.4 x 38.1 mm, white
Order No.	2657160000
Type	THM WO VIN 25.4/38.1 WS
GTIN (EAN)	4050118675290
Qty.	2,000 pc(s).
compatible printer	2599430000 2599440000

THM WO VIN 25.4/38.1 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	0.07 mm	Depth (inches)	0.003 inch
Height	25.4 mm	Height (inches)	1 inch
Width	38.1 mm	Width (inches)	1.5 inch
Net weight	0.117 g		

Temperatures

Operating temperature range	-40...80 °C
-----------------------------	-------------

General data

Adhesive	Polyacrylate adhesive	
Approval acc. to UL 969	No	
Colour	white	
Halogen	Yes	
Material	Vinyl film	
Number of markers per combination	1 Label reel = Conductor and cable markers	
Number of markers per packaging unit	Form of supply	Label reel
Number per roll	2,000	
Operating temperature range	-40...80 °C	
Operating temperature range, max.	80 °C	
Operating temperature range, min.	-40 °C	
Printing method	Thermal transfer	
Type of printing	neutral	
UL 94 flammability rating	V-0	
Width	38.1 mm	

Conductor and cable markers

Conductor O.D.	4 - 8 mm	Conductor O.D., max.	8 mm
Conductor O.D., min.	4 mm	Halogen	Yes
Wire connection cross section AWG, max.	AWG 6	Wire connection cross section AWG, min.	AWG 10

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ECLASS 9.0	27-40-04-01	ECLASS 9.1	27-40-04-01
ECLASS 10.0	27-40-04-01	ECLASS 11.0	27-28-11-02
ECLASS 12.0	27-28-11-02	ECLASS 13.0	27-28-11-02

Environmental Product Compliance

REACH SVHC	/
------------	---

Approvals

ROHS	Conform
------	---------

Downloads


Catalogues	Catalogues in PDF-format
------------	--

THM WO VIN 25.4/38.1 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



THM WO VIN 25.4/38.1 WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Ink ribbons**

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	RIBBON MM 110/360 SW	Version
Order No.	2005070000	Ink ribbon
GTIN (EAN)	4050118390049	
Qty.	1 pc(s).	