

**FIT 25 GN****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

Our feed-in modules facilitate handling when feeding the system. For example, the bending radius of the cable can be reduced by using a feed-in module with side entry.

**General ordering data**

Version	Auxiliary connection (terminal), 25 mm <sup>2</sup>
Order No.	<a href="#">2659050000</a>
Type	FIT 25 GN
GTIN (EAN)	4050118671483
Qty.	10 pc(s).

**FIT 25 GN****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	19.5 mm	Depth (inches)	0.768 inch
Height	34 mm	Height (inches)	1.339 inch
Width	13.5 mm	Width (inches)	0.531 inch
Net weight	10 g		

**Material data**

Colour	grey
--------	------

**Rating data**

Rated cross-section	25 mm <sup>2</sup>	Rated current	101 A
---------------------	--------------------	---------------	-------

**Classifications**

ETIM 6.0	EC002848	ETIM 7.0	EC002848
ETIM 8.0	EC002848	ETIM 9.0	EC002848
ECLASS 9.0	27-14-11-92	ECLASS 9.1	27-14-11-92
ECLASS 10.0	27-14-11-92	ECLASS 11.0	27-14-11-92
ECLASS 12.0	27-14-11-92	ECLASS 13.0	27-25-03-08

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--