

FIT 50 GN/F**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Our feed-in modules facilitate handling when feeding the system. For example, the bending radius of the cable can be reduced by using a feed-in module with side entry.

General ordering data

Version	Auxiliary connection (terminal), 50 mm ²
Order No.	2659090000
Type	FIT 50 GN/F
GTIN (EAN)	4050118671445
Qty.	3 pc(s).

FIT 50 GN/F**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	27 mm	Depth (inches)	1.063 inch
Height	39.7 mm	Height (inches)	1.563 inch
Width	17.8 mm	Width (inches)	0.701 inch
Net weight	30 g		

Material data

Colour	grey
--------	------

General

Number of poles	1
-----------------	---

Rating data

Rated cross-section	50 mm ²	Rated current	150 A
---------------------	--------------------	---------------	-------

Classifications

ETIM 6.0	EC002848	ETIM 7.0	EC002848
ETIM 8.0	EC002848	ETIM 9.0	EC002848
ECLASS 9.0	27-14-11-92	ECLASS 9.1	27-14-11-92
ECLASS 10.0	27-14-11-92	ECLASS 11.0	27-14-11-92
ECLASS 12.0	27-14-11-92	ECLASS 13.0	27-25-03-08

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	08c53393-8863-492c-addc-d040b46da0d3

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--