

**CB-HTR 365/7,5 BK****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Our heat-stabilised cable ties made of polyamide 6.6 are suitable for continuous use at temperatures up to +125°C.

**General ordering data**

Version	Cable ties, 7.5 x 365 mm, Polyamide 66, 540 N
Order No.	<a href="#">2659420000</a>
Type	CB-HTR 365/7,5 BK
GTIN (EAN)	4050118682885
Qty.	100 pc(s).

**CB-HTR 365/7,5 BK****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Height	365 mm	Height (inches)	14.37 inch
Width	7.5 mm	Width (inches)	0.295 inch
Net weight	4.21 g		

**Temperatures**

Operating temperature range	-40...125 °C	Continuous operating temp., min.	-40 °C
Continuous operating temp., max.	125 °C		

**Installation materials**

Bundle diameter, max.	100 mm	Bundle diameter, min.	8 mm
Cable diameter, max.	100 mm	For re-opening	No
Halogen	No	Material	Polyamide 66
Operating temperature range, max.	125 °C	Operating temperature range, min.	-40 °C
Tensile strength	540 N	Tensile strength (Pound-force)	121 lbf
UL 94 flammability rating	V-2	UV-resistant	No

**Classifications**

ETIM 6.0	EC000046	ETIM 7.0	EC000046
ETIM 8.0	EC000046	ETIM 9.0	EC000046
ECLASS 9.0	27-14-07-02	ECLASS 9.1	27-14-07-02
ECLASS 10.0	27-14-07-02	ECLASS 11.0	27-14-07-02
ECLASS 12.0	27-14-07-02	ECLASS 13.0	27-14-07-02

**Approvals**

Approvals



ROHS

Conform

**Downloads**

Approval/Certificate/Document of Conformity

[EU Declaration of Conformity](#)

Catalogues

[Catalogues in PDF-format](#)

### CB-HTR 365/7,5 BK

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

