

CB-VT 365/7,5 WT**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

Our self-extinguishing cable ties are suitable for environments with increased fire protection requirements. They comply with EN45545 and are suitable for use in rail vehicles.

General ordering data

Version	Cable ties, 7.5 x 365 mm, Polyamide 66, 540 N
Order No.	2659540000
Type	CB-VT 365/7,5 WT
GTIN (EAN)	4050118683004
Qty.	100 pc(s).

CB-VT 365/7,5 WT**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Height	365 mm	Height (inches)	14.37 inch
Width	7.5 mm	Width (inches)	0.295 inch
Net weight	4.21 g		

Temperatures

Operating temperature range	-40...85 °C	Continuous operating temp., min.	-40 °C
Continuous operating temp., max.	85 °C		

Installation materials

Bundle diameter, max.	100 mm	Bundle diameter, min.	8 mm
Cable diameter, max.	100 mm	For re-opening	No
Halogen	No	Material	Polyamide 66
Operating temperature range, max.	85 °C	Operating temperature range, min.	-40 °C
Tensile strength	540 N	Tensile strength (Pound-force)	121 lbf
UL 94 flammability rating	V-0	UV-resistant	No

Classifications

ETIM 6.0	EC000046	ETIM 7.0	EC000046
ETIM 8.0	EC000046	ETIM 9.0	EC000046
ECLASS 9.0	27-14-07-02	ECLASS 9.1	27-14-07-02
ECLASS 10.0	27-14-07-02	ECLASS 11.0	27-14-07-02
ECLASS 12.0	27-14-07-02	ECLASS 13.0	27-14-07-02
ECLASS 14.0	27-14-07-02		

Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	EU Declaration of Conformity
Catalogues	Catalogues in PDF-format

CB-VT 365/7,5 WT

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

