

V-TEST II ADP**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**V-TEST II**

- Testing device for pluggable overvoltage protection VPU AC and VPU PV series
- Device for implementing the IEC 62305-3 standard (Periodic test)
- Handy device with integrated rechargeable battery set for on-site use measurements
- QR code leads to check value table
- Intuitive user guidance (English)

The V-TEST II is a compact, portable test unit for pluggable overvoltage protection of VPU AC and VPU PV series. The test device can be used to test surge protection in accordance with the test periods required by IEC62305-3. The measuring result of the protective element is shown in a backlit display. To determine the status of the protective element, the measurement result must be verified with the aid of the test table.

General ordering data

Version	Lightning and surge protection, Adapter
Order No.	2661050000
Type	V-TEST II ADP
GTIN (EAN)	4050118704150
Qty.	1 pc(s).

V-TEST II ADP

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	60 mm	Depth (inches)	2.362 inch
Height	52 mm	Height (inches)	2.047 inch
Width	109 mm	Width (inches)	4.291 inch
Net weight	500 g		

Temperatures

Storage temperature	-10 °C...60 °C	Operating temperature	0 °C...40 °C
Humidity	25 - 75%, no condensation		

General data

Colour	black	Protection degree	IP20
UL 94 flammability rating	V-0		

Rated data IEC / EN

Standards	EN 61010-1, EN 61326-1
-----------	------------------------

Technical specifications for tester

UL 94 flammability rating	V-0
---------------------------	-----

Classifications

ETIM 6.0	EC002495	ETIM 7.0	EC002495
ETIM 8.0	EC002495	ETIM 9.0	EC002495
ECLASS 9.0	27-20-11-14	ECLASS 9.1	27-20-11-14
ECLASS 10.0	27-20-11-14	ECLASS 11.0	27-20-11-14
ECLASS 12.0	27-20-11-14	ECLASS 13.0	27-20-11-14

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--