

**SAIEND 1/4 M8G 3P****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Passive M12 distributors are available in all conceivable forms and configurations. Furthermore, a number of special versions, e.g. SAI distributors for EX zones or the ergonomic M8, are available only from Weidmüller. These innovative products are backed up by numerous proprietary rights.

**General ordering data**

Version	M8, LED: , LED initiator: , Wiring type:
Order No.	<a href="#">2662450000</a>
Type	SAIEND 1/4 M8G 3P
GTIN (EAN)	4050118677379
Qty.	1 pc(s).

## SAIEND 1/4 M8G 3P

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Dimensions and weights

Net weight	5 g
------------	-----

## Temperatures

Operating temperature	-25 - 85°C
-----------------------	------------

## General technical data

Protection degree	IP67	Number of poles	3
Connection thread	M8	Pollution severity	3
Plugging cycles	≥ 100		

## Technical data cable

Number of poles	3
-----------------	---

## Classifications

ETIM 6.0	EC000448	ETIM 7.0	EC000448
ETIM 8.0	EC000448	ETIM 9.0	EC000448
ECLASS 9.0	19-07-04-03	ECLASS 9.1	19-17-01-90
ECLASS 10.0	19-07-04-03	ECLASS 11.0	19-07-04-03
ECLASS 12.0	19-07-04-03	ECLASS 13.0	19-07-04-03

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	1c533b66-fcff-4da5-b89f-fd55fbf5cb55

## Approvals

Approvals



## Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

## SAIEND 1/4 M8G 3P

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

# Drawings

