

**IE-SFP-1FE-SM-30****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Features of SFP-Transceiver series**

- Huge variety of transceiver types for several transmission speeds (up to 10 Gigabit Ethernet) and distances (up to 60 km)
- BiDi SFP models for communication via single fiber
- Easy control of transceiver status due to support of Digital Diagnostic Monitoring (DDM)
- Hot pluggable (during operation)
- Class 1 laser product, EN60825-1 compliant
- Applicable for switches of the Eco-, Advanced- and SubstationLine

**General ordering data**

Version	SFP Transceiver, 100 Mbps, Singlemode, LC-Duplex, 30 km, -40 °C...85 °C
Order No.	<a href="#">2682460000</a>
Type	IE-SFP-1FE-SM-30
GTIN (EAN)	4050118692259
Qty.	1 pc(s).

## IE-SFP-1FE-SM-30

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Net weight	17.5 g
------------	--------

## Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...85 °C
Humidity	5 to 95 % (non-condensing)		

## EMC conformity and approvals

EMC standards	EN 55032, EN 55035	Safety standard	UL 62368-1
---------------	--------------------	-----------------	------------

## Environmental conditions

Humidity	5 to 95 % (non-condensing)	Operating temperature, max.	85 °C
Operating temperature, min.	-40 °C	Storage temperature, max.	85 °C
Storage temperature, min.	-40 °C		

## Fibre optic transceiver characteristics

Transmission rate	100 Mbps	
Digital diagnostic monitor function (DDM)	Supported	
Transceiver type	Singlemode	
Connector type	LC-Duplex	
Transmission distance, typ.	30 km	
Wavelength	typ.	1,310 nm
	Wavelength	TX
	min.	1,280 nm
	max.	1,340 nm
	Wavelength	RX
	min.	1,260 nm
Receive power	min.	-34 dBm
	max.	-3 dBm
Transmission power	min.	-15 dBm
	max.	-8 dBm
Link-budget	19 dB	

## Guarantee

Time interval	3 years
---------------	---------

## Power supply

Voltage supply	3.3 V (via Ethernet switch)
----------------	-----------------------------

## Technical data

Type of mounting	Insert in SFP slot
------------------	--------------------

**IE-SFP-1FE-SM-30****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Classifications**

ETIM 6.0	EC001121	ETIM 7.0	EC001121
ETIM 8.0	EC003628	ETIM 9.0	EC003628
ECLASS 9.1	27-44-02-92	ECLASS 10.0	27-44-02-92
ECLASS 11.0	19-17-03-03	ECLASS 12.0	19-17-03-03
ECLASS 13.0	19-17-03-03		

**Environmental Product Compliance**

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

**Approvals**

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E230683

**Downloads**

Approval/Certificate/Document of Conformity	<a href="#">EU Declaration of Conformity</a> <a href="#">RCM Declaration of Conformity</a> <a href="#">UK Declaration of Conformity</a>
Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**IE-SFP-1FE-SM-30****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****LC-Duplex**

Mounting rail outlet, LC duplex junction design according to IEC 61754-20

**General ordering data**

Type	IE-TO-LCD-SM	Version
Order No.	<a href="#">8947020000</a>	Mounting rail outlet, fibre-optic, LC Duplex, Singlemode, IP20
GTIN (EAN)	4032248735037	
Qty.	10 pc(s).	