

IE-SFP-1GE-SM-10-BIDI-TX1310**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Features of SFP-Transceiver series**

- Huge variety of transceiver types for several transmission speeds (up to 10 Gigabit Ethernet) and distances (up to 60 km)
- BiDi SFP models for communication via single fiber
- Easy control of transceiver status due to support of Digital Diagnostic Monitoring (DDM)
- Hot pluggable (during operation)
- Class 1 laser product, EN60825-1 compliant
- Applicable for switches of the Eco-, Advanced- and SubstationLine

General ordering data

Version	SFP Transceiver, 1000 Mbps, Singlemode BiDi, LC-Simplex, 10 km, -40 °C...85 °C
Order No.	2682520000
Type	IE-SFP-1GE-SM-10-BIDI-TX1310
GTIN (EAN)	4050118692198
Qty.	1 pc(s).

IE-SFP-1GE-SM-10-BIDI-TX1310**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Net weight	17.5 g
------------	--------

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...85 °C
Humidity	5 to 95 % (non-condensing)		

EMC conformity and approvals

EMC standards	EN 55032, EN 55035	Safety standard	UL 62368-1
---------------	--------------------	-----------------	------------

Environmental conditions

Humidity	5 to 95 % (non-condensing)	Operating temperature, max.	85 °C
Operating temperature, min.	-40 °C	Storage temperature, max.	85 °C
Storage temperature, min.	-40 °C		

Fibre optic transceiver characteristics

Transmission rate	1000 Mbps	
Digital diagnostic monitor function (DDM)	Supported	
Transceiver type	Singlemode BiDi	
Connector type	LC-Simplex	
Transmission distance, typ.	10 km	
Wavelength	Wavelength	TX
	typ.	1,310 nm
	Wavelength	RX
	typ.	1,550 nm
	Wavelength	TX
	min.	1,270 nm
	max.	1,355 nm
	Wavelength	RX
	min.	1,470 nm
	max.	1,600 nm
Receive power	min.	-20 dBm
	max.	-3 dBm
Transmission power	min.	-9 dBm
	max.	-3 dBm
Link-budget	11 dB	
Note	BiDi-SFP transceivers must be used in pairs (e.g. IE-SFP-1GE-SM-10-BIDI-TX1310 and IE-SFP-1GE-SM-10-BIDI-TX1550 or IE-SFP-1GE-SM-20-BIDI-TX1310 and IE-SFP-1GE-SM-20-BIDI-TX1550).	

Guarantee

Time interval	3 years
---------------	---------

Power supply

Voltage supply	3.3 V (via Ethernet switch)
----------------	-----------------------------

IE-SFP-1GE-SM-10-BIDI-TX1310

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Technical data

Type of mounting	Insert in SFP slot
------------------	--------------------

Classifications

ETIM 6.0	EC001121	ETIM 7.0	EC001121
ETIM 8.0	EC003628	ETIM 9.0	EC003628
ECLASS 9.1	27-44-02-92	ECLASS 10.0	27-44-02-92
ECLASS 11.0	19-17-03-03	ECLASS 12.0	19-17-03-03
ECLASS 13.0	19-17-03-03	ECLASS 14.0	19-17-03-03

Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E230683

Downloads

Approval/Certificate/Document of Conformity	EU Declaration of Conformity RCM Declaration of Conformity UK Declaration of Conformity
Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format