

IE-PS-M12X-90-P-TH-CG**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The 8pole M12 Mini crimp cable connector with X-coding and 90° cable exit is with compact dimensions and 8 cable exit positions predestined for difficult installation conditions. The cable clamp version with the wide cable clamp ranges from 4 up to 9 mm plus the fully shielded housing together with the shielded strain relief is the universal fail-safe solution for all common cables on the market.

General ordering data

Order No.	2702710000
Type	IE-PS-M12X-90-P-TH-CG
GTIN (EAN)	4050118765328
Qty.	1 pc(s).

IE-PS-M12X-90-P-TH-CG**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight	20.5 g
------------	--------

Technical data customisable plug-in connectors

Cable diameter	4...9 mm	Cable diameter, max.	9 mm
Cable diameter, min.	4 mm	Category	Cat.6A / Class EA (ISO/IEC 11801 2010)
Coding	X-coded	Conductor cross-section, max.	0.34 mm ²
Conductor cross-section, min.	0.14 mm ²	Connection cross-section, max.	0.34 mm ²
Connection cross-section, min.	0.14 mm ²	Contact surface	Gold-plated
Housing main material	Cu alloy Ni plated	Number of poles	4
Plugging cycles	≥ 500	Pollution severity	3
Protection degree	IP67 plugged	Rated current	2 A
Rated voltage	30 V	Shield connection	Yes, screwed
Temperature range of housing	-40 ... +85 °C	Type of connection	Crimp connection

General Info

Number of poles	4	Connection 1	M12
Connection 2	Crimp	Housing main material	Cu alloy Ni plated
Category	Cat.6A / Class EA (ISO/IEC 11801 2010)	Connection thread	M12
Contact surface	Gold-plated	Protection degree	IP67 plugged
Plugging cycles	≥ 500		

Electrical properties

Rated voltage	30 V
---------------	------

General standards

Connector standard	IEC 61076-2-109
--------------------	-----------------

Standards

Connector standard	IEC 61076-2-109
--------------------	-----------------

Classifications

ETIM 6.0	EC002635	ETIM 7.0	EC002635
ETIM 8.0	EC002635	ETIM 9.0	EC002635
ECLASS 9.0	27-44-01-02	ECLASS 9.1	27-44-01-03
ECLASS 10.0	27-44-01-02	ECLASS 11.0	27-44-01-02
ECLASS 12.0	27-44-01-16	ECLASS 13.0	27-44-01-02

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Approvals

ROHS	Conform
------	---------

IE-PS-M12X-90-P-TH-CG

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

Engineering Data

[CAD data – STEP](#)

Catalogues

[Catalogues in PDF-format](#)


IE-PS-M12X-90-P-TH-CG

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany


www.weidmueller.com

Drawings


Dimensioned drawing



Dimensioned drawing



Pole scheme



IE-PS-M12X-90-P-TH-CG**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****M12X crimp contacts**

Machined precision crimp contacts for M12X

**General ordering data**

Type	IE-PIC-M12X-P-22/26	Version
Order No.	2664880000	Contact, Pin
GTIN (EAN)	4050118765342	
Qty.	100 pc(s).	

...for M12

Weidmüller offers a wide range of tools and accessories for sensor-actuator cabling.

General ordering data

Type	SAI-TMCSK	Version
Order No.	1381690000	Pressing tool
GTIN (EAN)	4050118183870	
Qty.	1 pc(s).	