

SCCB TTB 6/3**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The short circuit bridge can be simply and quickly inserted into the terminal blocks. If several levers are connected simultaneously with the lever connector, the make before break can be realised. Once mounted, the short circuit bridge cannot be removed from the application.

General ordering data

Version	Cross-connector (terminal), Plugged, Number of poles: 3, Pitch in mm (P): 8.10, Insulated: Yes, 30 A, orange
Order No.	2710200000
Type	SCCB TTB 6/3
GTIN (EAN)	4050118847994
Qty.	25 pc(s).

SCCB TTB 6/3

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	13.47 mm	Depth (inches)	0.53 inch
Height	14.06 mm	Height (inches)	0.554 inch
Width	24.1 mm	Width (inches)	0.949 inch
Net weight	4.2 g		

Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

Material data

Material	Wemid	Colour	orange
UL 94 flammability rating	V-0		

System specifications

Version	Cross-connector
---------	-----------------

Additional technical data

Explosion-tested version	No	Type of fixing	Plugged
Type of mounting	Plugged		

Dimensions

Pitch in mm (P)	8.1 mm
-----------------	--------

General

Number of poles	3
-----------------	---

Rating data

Rated voltage	500 V	Rated current	30 A
---------------	-------	---------------	------

Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ECLASS 9.0	27-14-11-40	ECLASS 9.1	27-14-11-40
ECLASS 10.0	27-14-11-40	ECLASS 11.0	27-14-11-40
ECLASS 12.0	27-14-11-40	ECLASS 13.0	27-25-03-03

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format