

TS TTB 6 OR**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The test socket is used to connect test devices with a standard 4.0 plug with widths up to 10 mm into the terminal. Test sockets are arranged at an angle, therefore all standard measurements (even adjoining) can be realised within the terminal width of 8.1 mm. Once mounted, the test socket cannot be removed from the application.

General ordering data

Version	Socket (terminal), Depth: 51.3 mm
Order No.	2710470000
Type	TS TTB 6 OR
GTIN (EAN)	4050118880649
Qty.	48 pc(s).

TS TTB 6 OR**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	51.3 mm	Depth (inches)	2.02 inch
Height	9.4 mm	Height (inches)	0.37 inch
Width	6.3 mm	Width (inches)	0.248 inch
Net weight	1.1 g		

Temperatures

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-60 °C
Continuous operating temp., max.	130 °C		

Material data

Material	Wemid	Colour	orange
UL 94 flammability rating	V-0		

Additional technical data

Type of fixing	Plugged	Type of mounting	Plug
----------------	---------	------------------	------

Classifications

ETIM 6.0	EC002848	ETIM 7.0	EC002848
ETIM 8.0	EC002848	ETIM 9.0	EC002848
ECLASS 9.0	27-14-11-92	ECLASS 9.1	27-14-11-92
ECLASS 10.0	27-14-11-92	ECLASS 11.0	27-14-11-92
ECLASS 12.0	27-14-11-92	ECLASS 13.0	27-25-03-90

Approvals

ROHS	Conform
------	---------

Downloads


Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format

TS TTB 6 OR

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



TS TTB 6 OR

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings

