

CH-HOAB-XXXX-06-0200-AI**Weidmüller Interface GmbH & Co. KG**


Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product similar to illustration



The increasingly networked industrial world goes hand in hand with the modularization of machines and systems. Functions from the control cabinet are increasingly being moved to field level, which drives up the amount of cabling required.

Our ready-for-connection cable assemblies can be used wiring in field level and for transmitting data or power in various applications. The Plug & Produce solution by Weidmüller are fully tested and will lead to simplification of assembly on your machine. This allows you to focus on your core competencies and further increase your efficiency.

With our broad product portfolio of certified components, we offer you a wide diversification so that we can provide you the perfect solution for your application.

If you cannot find the cable assembly you are looking for despite our continuously growing portfolio, we can also offer you different length variants and customer-specific solutions.

General ordering data

Version	Heavy duty connector assemblies, Socket connector, Lapp ÖLFLEX® CLASSIC 110 BK 7G2.5 or similar, Shielded: No, Number of poles: 6
Order No.	2712410200
Type	CH-HOAB-XXXX-06-0200-AI
GTIN (EAN)	4050118779271
Qty.	1 pc(s).

CH-HOAB-XXXX-06-0200-AI

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	749.118 g
------------	-----------

Temperatures

Limit temperature	-40 °C ... 80 °C
-------------------	------------------

Technical specifications for cable

Bending radius, min., moving	10 x cable diameter	Bending radius, min., stationary	4 x cable diameter
Cable length	2	Core cross-section	2.5 mm ²
Halogen	Yes	Insulation	PVC
Number of poles	6	Number of wires	7
Outside diameter	11.1 mm	Sheath material	PVC
Sheathing colour	black	Shielded	No
Temperature range, moving	-15...70 °C	Temperature range, stationary	-40...80 °C

General technical data

Protection degree	IP65	Rated voltage	500 V
Version	Socket connector		

General Technical Data

Number of poles	6	Pin arrangement	1:1, numbered cores
Protection degree	IP65	Rated voltage	500 V

Technical Specifications Connector

Connector	Connector description	Connector 1
	Cable entry	straight
	Housing main material	Plastic
	Number of poles	6
	Series	HQ
	Size	HQ
	Type	Female
	Individual components connector	HDC HQP TOLU 1PG16 HDC HQ 4/2 FC HDC C HX BM2.5AG HDC-C-HD-BM2.5AG VG 16 HQ K68 9-13

Technical specifications for cable

Bending radius, min., moving	10 x cable diameter	Bending radius, min., stationary	4 x cable diameter
Cable length	2	Core cross-section	2.5 mm ²
Halogen	Yes	Insulation	PVC
Line type	Lapp ÖLFLEX® CLASSIC 110 BK 7G2.5 or similar	Number of wires	7
Outside diameter	11.1 mm	Sheath material	PVC
Sheathing colour	black	Shielded	No
Temperature range, moving	-15...70 °C	Temperature range, moving, max.	70 °C
Temperature range, moving, min.	-15 °C	Temperature range, stationary	-40...80 °C
Temperature range, stationary, max.	80 °C	Temperature range, stationary, min.	-40 °C

CH-HOAB-XXXX-06-0200-AI**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germanywww.weidmueller.com**Technical data****Classifications**

ETIM 6.0	EC001576	ETIM 7.0	EC001576
ETIM 8.0	EC001576	ETIM 9.0	EC001576
ECLASS 9.0	27-06-04-02	ECLASS 9.1	27-06-91-90
ECLASS 10.0	27-06-04-02	ECLASS 11.0	27-06-04-02
ECLASS 12.0	27-06-04-02	ECLASS 13.0	27-06-04-02

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1 Potassium perfluorobutane sulfonate 29420-49-3
SCIP	81ca46c4-2930-4739-aa54-e07d33c98f2c
RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--

CH-HOAB-XXXX-06-0200-AI**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Angled bulkhead housing



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection. The HQ version now offers particular protection - the bulkhead housing (cover and metal clamp) can be secured with a padlock.

General ordering data

Type	HDC HQP AWLU	Version	
Order No.	1003060000		HDC enclosures, Size: HQ, Protection degree: IP65 (in plugged condition), Bulkhead housing, Side-locking clamp on lower side,
GTIN (EAN)	4032248697991		
Qty.	1 pc(s).		Standard

Bulkhead housing



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection. The HQ version now offers particular protection - the bulkhead housing (cover and metal clamp) can be secured with a padlock.

General ordering data

Type	HDC HQP ALU	Version	
Order No.	1003040000		HDC enclosures, Size: HQ, Protection degree: IP65 (in plugged condition), Bulkhead housing, Side-locking clamp on lower side,
GTIN (EAN)	4032248697977		
Qty.	1 pc(s).		Standard

CH-HOAB-XXXX-06-0200-AI**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories**

Type	HDC HQP ALU CS	Version
Order No.	1354950000	HDC enclosures, Size: HQ, Protection degree: IP65 (in plugged condition), Bulkhead housing, Side-locking clamp on lower side,
GTIN (EAN)	4050118157215	Standard
Qty.	1 pc(s).	

4/2-pole

The HQ series - big features in a compact design. The electrical characteristics speak for themselves. You can also use the proven HD and HX crimp contacts here. The wire connection level is designed for crimp contacts. The proven crimp connection has been in standard use for decades.

Crimp contacts are not included in the scope of delivery of inserts.

Pole count: **4/2 (+PE)**

Rated current: **40/10 A**

Rated voltage: **690 / 250 V**

Rated voltage acc. to UL/CSA: **600 V AC/DC**

Crimp connection

General ordering data

Type	HDC HQ 4/2 MC	Version
Order No.	1003170000	HDC insert, Male, 690 V, 40 A, Number of poles: 6, Crimp connection,
GTIN (EAN)	4032248698165	Size: HQ
Qty.	1 pc(s).	

CH-HOAB-XXXX-06-0200-AI**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Base housing



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection. The HQ version now offers particular protection - the bulkhead housing (cover and metal clamp) can be secured with a padlock.

General ordering data

Type	HDC HQP SLU 1PG16	Version
Order No.	1003110000	HDC enclosures, Size: HQ, Protection degree: IP65 (in plugged condition), Base housing, Side-locking clamp on lower side, Standard,
GTIN (EAN)	4032248698042	Size of cable entries: PG 16
Qty.	1 pc(s).	

CH-HOAB-XXXX-06-0200-AI

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Coupling housing



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection. The HQ version now offers particular protection - the bulkhead housing (cover and metal clamp) can be secured with a padlock.

General ordering data

Type	HDC HQP KOLU 1PG16	Version
Order No.	1003120000	HDC enclosures, Size: HQ, Protection degree: IP65 (in plugged condition), Coupling housing, Side-locking clamp on lower side,
GTIN (EAN)	4032248698059	Standard, Size of cable entries: PG 16
Qty.	1 pc(s).	

Bulkhead housing



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection. The HQ version now offers particular protection - the bulkhead housing (cover and metal clamp) can be secured with a padlock.

General ordering data

Type	HDC HQM ALU CS	Version
Order No.	1251680000	HDC enclosures, Size: HQ, Protection degree: IP65 (in plugged condition), Bulkhead housing, Side-locking clamp on lower side,
GTIN (EAN)	4050118051803	Standard
Qty.	1 pc(s).	

CH-HOAB-XXXX-06-0200-AI**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories**

Type	HDC HQM ALU	Version
Order No.	1003050000	HDC enclosures, Size: HQ, Protection degree: IP65 (in plugged
GTIN (EAN)	4032248697984	condition), Bulkhead housing, Side-locking clamp on lower side,
Qty.	1 pc(s).	Standard