

**CH-HPBC-HPBD-08-0200-AA****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Product similar to illustration

The increasingly networked industrial world goes hand in hand with the modularization of machines and systems. Functions from the control cabinet are increasingly being moved to field level, which drives up the amount of cabling required.

Our ready-for-connection cable assemblies can be used wiring in field level and for transmitting data or power in various applications. The Plug & Produce solution by Weidmüller are fully tested and will lead to simplification of assembly on your machine. This allows you to focus on your core competencies and further increase your efficiency.

With our broad product portfolio of certified components, we offer you a wide diversification so that we can provide you the perfect solution for your application.

If you cannot find the cable assembly you are looking for despite our continuously growing portfolio, we can also offer you different length variants and customer-specific solutions.

**IP65****2.5 mm²****General ordering data**

Version	Heavy duty connector assemblies, Pin, Socket connector, Helukabel JZ-500 10G2.5 or similar, Shielded: No, Number of poles: 8
Order No.	<a href="#">2712450200</a>
Type	CH-HPBC-HPBD-08-0200-AA
GTIN (EAN)	4050118779721
Qty.	1 pc(s).

**CH-HPBC-HPBD-08-0200-AA****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Net weight	815.417 g
------------	-----------

**Temperatures**

Limit temperature	-40 °C ... 80 °C
-------------------	------------------

**Technical specifications for cable**

Bending radius, min., moving	7.5 x cable diameter	Bending radius, min., stationary	4 x cable diameter
Cable length	2	Core cross-section	2.5 mm <sup>2</sup>
Halogen	Yes	Insulation	PVC
Number of poles	8	Number of wires	10
Outside diameter	14.8 mm	Sheath material	PVC
Sheathing colour	grey	Shielded	No
Temperature range, moving	-15...80 °C	Temperature range, stationary	-40...80 °C

**General technical data**

Protection degree	IP65	Rated voltage	500 V
Version	Pin, Socket connector		

**General Technical Data**

Number of poles	8	Pin arrangement	1:1, numbered cores
Protection degree	IP65	Rated voltage	500 V

**Technical Specifications Connector**

Connector	Connector description	Connector 1
	Cable entry	angled
	Housing main material	Plastic
	Number of poles	8
	Series	HQ
	Size	HQ
	Type	Male
	Individual components connector	<a href="#">HDC HQP TSLU 1PG16 HDC HQ 8 MC HDC-C-HE-SM2.5AG VG 16 HQ K68 11.5-15.5</a>
	Connector description	Connector 2
	Cable entry	angled
	Housing main material	Plastic
	Number of poles	8
	Series	HQ
	Size	HQ
	Type	Female
	Individual components connector	<a href="#">HDC HQP TSLU 1PG16 HDC HQ 8 FC HDC-C-HE-BM2.5AG VG 16 HQ K68 11.5-15.5</a>

**CH-HPBC-HPBD-08-0200-AA****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Technical specifications for cable**

Bending radius, min., moving	7.5 x cable diameter	Bending radius, min., stationary	4 x cable diameter
Cable length	2	Core cross-section	2.5 mm <sup>2</sup>
Halogen	Yes	Insulation	PVC
Line type	Helukabel JZ-500 10G2.5 or similar	Number of wires	10
Outside diameter	14.8 mm	Sheath material	PVC
Sheathing colour	grey	Shielded	No
Temperature range, moving	-15...80 °C	Temperature range, moving, max.	80 °C
Temperature range, moving, min.	-15 °C	Temperature range, stationary	-40...80 °C
Temperature range, stationary, max.	80 °C	Temperature range, stationary, min.	-40 °C

**Classifications**

ETIM 6.0	EC001576	ETIM 7.0	EC001576
ETIM 8.0	EC001576	ETIM 9.0	EC001576
ECLASS 9.0	27-06-04-02	ECLASS 9.1	27-06-91-90
ECLASS 10.0	27-06-04-02	ECLASS 11.0	27-06-04-02
ECLASS 12.0	27-06-04-02	ECLASS 13.0	27-06-04-02

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1 Potassium perfluorobutane sulfonate 29420-49-3 6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol 119-47-1
SCIP	1344e4a2-b558-4ad0-95d1-5c6df3fdd75e

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--

**CH-HPBC-HPBD-08-0200-AA****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Bulkhead housing**

The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection. The HQ version now offers particular protection - the bulkhead housing (cover and metal clamp) can be secured with a padlock.

**General ordering data**

Type	HDC HQP ALU CS	Version
Order No.	<a href="#">1354950000</a>	HDC enclosures, Size: HQ, Protection degree: IP65 (in plugged condition), Bulkhead housing, Side-locking clamp on lower side,
GTIN (EAN)	4050118157215	Standard
Qty.	1 pc(s).	
Type	HDC HQP ALU	Version
Order No.	<a href="#">1003040000</a>	HDC enclosures, Size: HQ, Protection degree: IP65 (in plugged condition), Bulkhead housing, Side-locking clamp on lower side,
GTIN (EAN)	4032248697977	Standard
Qty.	1 pc(s).	

**CH-HPBC-HPBD-08-0200-AA****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Bulkhead housing**

The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection. The HQ version now offers particular protection - the bulkhead housing (cover and metal clamp) can be secured with a padlock.

**General ordering data**

Type	HDC HQM ALU CS	Version
Order No.	<a href="#">1251680000</a>	HDC enclosures, Size: HQ, Protection degree: IP65 (in plugged condition), Bulkhead housing, Side-locking clamp on lower side,
GTIN (EAN)	4050118051803	Standard
Qty.	1 pc(s).	
Type	HDC HQM ALU	Version
Order No.	<a href="#">1003050000</a>	HDC enclosures, Size: HQ, Protection degree: IP65 (in plugged condition), Bulkhead housing, Side-locking clamp on lower side,
GTIN (EAN)	4032248697984	Standard
Qty.	1 pc(s).	

**CH-HPBC-HPBD-08-0200-AA****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Angled bulkhead housing**

The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection. The HQ version now offers particular protection - the bulkhead housing (cover and metal clamp) can be secured with a padlock.

**General ordering data**

Type	HDC HQP AWLU	Version
Order No.	<a href="#">1003060000</a>	HDC enclosures, Size: HQ, Protection degree: IP65 (in plugged condition), Bulkhead housing, Side-locking clamp on lower side,
GTIN (EAN)	4032248697991	Standard
Qty.	1 pc(s).	

**CH-HPBC-HPBD-08-0200-AA****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Base housing**

The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection. The HQ version now offers particular protection - the bulkhead housing (cover and metal clamp) can be secured with a padlock.

**General ordering data**

Type	HDC HQP SLU 1PG16	Version	
Order No.	<a href="#">1003110000</a>		HDC enclosures, Size: HQ, Protection degree: IP65 (in plugged condition), Base housing, Side-locking clamp on lower side, Standard,
GTIN (EAN)	4032248698042		Size of cable entries: PG 16
Qty.	1 pc(s).		

**8-pole**

A small size but quite big. The electrical values speak for themselves. Proven HE crimp contacts can also be used here.

**Pole count: 8 (+PE)****Rated current: 16 A****Rated voltage: 500 V****Nominal voltage acc. to UL/CSA: 600 V AC/DC****Crimp connection****General ordering data**

Type	HDC HQ 8 MC	Version	
Order No.	<a href="#">1919970000</a>		HDC insert, Male, 500 V, 16 A, Number of poles: 8, Crimp connection,
GTIN (EAN)	4032248557943		Size: HQ
Qty.	1 pc(s).		
Type	HDC HQ 8 FC	Version	
Order No.	<a href="#">1919980000</a>		HDC insert, Female, 500 V, 16 A, Number of poles: 8, Crimp connection, Size: HQ
GTIN (EAN)	4032248557950		
Qty.	1 pc(s).		

**CH-HPBC-HPBD-08-0200-AA****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Coupling housing**

The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection. The HQ version now offers particular protection - the bulkhead housing (cover and metal clamp) can be secured with a padlock.

**General ordering data**

Type	HDC HQP KOLU 1PG16	Version
Order No.	<a href="#">1003120000</a>	HDC enclosures, Size: HQ, Protection degree: IP65 (in plugged condition), Coupling housing, Side-locking clamp on lower side,
GTIN (EAN)	4032248698059	Standard, Size of cable entries: PG 16
Qty.	1 pc(s).	