

HDC XX6A02 OOXXXDM-1000**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Compact**

The new two-pole bus module is extremely compact and can accommodate both megabit and gigabit data inserts. It enables the connection of 2 Gigabit Cat 6A cables (10 gigabit) to one module.

General ordering data

Version	
Order No.	2712681000
Type	HDC XX6A02 OOXXXDM-1000
GTIN (EAN)	4050118753028
Qty.	1 pc(s).

HDC XX6A02 OOXXXDM-1000**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Net weight	2,300 g
------------	---------

General data

Cable length	100 m	Category	Cat. 7 (ISO/IEC 11801)
Insulation strength	≥ 500 MΩ	Module side version	open
Number of poles	8	Opposite side version	open
Pollution severity	2	Rated current	0.5 A
Rated voltage	100 V		

Cable technical specifications

Cable length	100 m	Halogen	halogen-free, according to IEC 60754-1
Insulation	PE	Sheath material	PUR
Sheathing colour	green		

Classifications

ETIM 6.0	EC000830	ETIM 7.0	EC003249
ETIM 8.0	EC003249	ETIM 9.0	EC003249
ECLASS 9.0	27-06-18-05	ECLASS 9.1	27-06-90-90
ECLASS 10.0	27-06-18-01	ECLASS 11.0	27-06-18-01
ECLASS 12.0	27-06-18-01	ECLASS 13.0	27-06-18-01

Environmental Product Compliance

REACH SVHC	/
------------	---

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--