

VP HEX M16 PA6 GY**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	Blanking plugs, in closed state, M 16 x 1.5, 15 mm, Polyamide 6 (PA 6)
Order No.	2715740000
Type	VP HEX M16 PA6 GY
GTIN (EAN)	4050118805093
Qty.	50 pc(s).

VP HEX M16 PA6 GY**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Height	4.3 mm	Height (inches)	0.169 inch
Width	19 mm	Width (inches)	0.748 inch
Length	15 mm	Length (inches)	0.591 inch
Diameter	22 mm	Wall thickness, min.	0.5 mm
Wall thickness, max.	14 mm	Net weight	0.003 g

Temperatures

Operating temperature	-20 °C... 100 °C
-----------------------	------------------

General information

Cable glands	metric	Diameter of sealing ring	16 mm
External thread	M 16 x 1.5	Halogen	No
Length of thread	15 mm	Material	Polyamide 6 (PA 6)
Operating temperature range, max.	100 °C	Operating temperature range, min.	-20 °C
Pitch of thread	1.5 mm	Protection degree	IP65, IP68 - 5 bar (30 min.)
Standards	in accordance with UL94 V-2	Tightening torque	1.5 Nm
UL 94 flammability rating	V-2		

Classifications

ETIM 6.0	EC000451	ETIM 7.0	EC000451
ETIM 8.0	EC000451	ETIM 9.0	EC000451
ECLASS 9.0	27-14-44-25	ECLASS 9.1	27-14-44-33
ECLASS 10.0	27-14-44-25	ECLASS 11.0	27-14-44-25
ECLASS 12.0	27-14-08-05	ECLASS 13.0	27-14-08-05

Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--