

VP HEX M40 PA6 GY**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	Blanking plugs, in closed state, M 40 x 1.5, 18 mm, Polyamide 6 (PA 6)
Order No.	2715780000
Type	VP HEX M40 PA6 GY
GTIN (EAN)	4050118805437
Qty.	10 pc(s).

VP HEX M40 PA6 GY**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Height	8.5 mm	Height (inches)	0.335 inch
Width	46 mm	Width (inches)	1.811 inch
Length	18 mm	Length (inches)	0.709 inch
Diameter	53 mm	Wall thickness, min.	0.5 mm
Wall thickness, max.	17 mm	Net weight	0.024 g

Temperatures

Operating temperature	-20 °C... 100 °C
-----------------------	------------------

General information

Cable glands	metric	Diameter of sealing ring	40 mm
External thread	M 40 x 1.5	Halogen	No
Length of thread	18 mm	Material	Polyamide 6 (PA 6)
Operating temperature range, max.	100 °C	Operating temperature range, min.	-20 °C
Pitch of thread	1.5 mm	Protection degree	IP65, IP68 - 5 bar (30 min.)
Standards	in accordance with UL94 V-2	Tightening torque	6 Nm
UL 94 flammability rating	V-2		

Classifications

ETIM 6.0	EC000451	ETIM 7.0	EC000451
ETIM 8.0	EC000451	ETIM 9.0	EC000451
ECLASS 9.0	27-14-44-25	ECLASS 9.1	27-14-44-33
ECLASS 10.0	27-14-44-25	ECLASS 11.0	27-14-44-25
ECLASS 12.0	27-14-08-05	ECLASS 13.0	27-14-08-05

Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--