

**VP HEX M50 PA6 GY****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

**General ordering data**

Version	Blanking plugs, in closed state, M 50 x 1.5, 18 mm, Polyamide 6 (PA 6)
Order No.	<a href="#">2715790000</a>
Type	VP HEX M50 PA6 GY
GTIN (EAN)	4050118805444
Qty.	10 pc(s).

**VP HEX M50 PA6 GY****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Height	9.5 mm	Height (inches)	0.374 inch
Width	55 mm	Width (inches)	2.165 inch
Length	18 mm	Length (inches)	0.709 inch
Diameter	63.5 mm	Wall thickness, min.	0.5 mm
Wall thickness, max.	17 mm	Net weight	0.035 g

**Temperatures**

Operating temperature	-20 °C...100 °C
-----------------------	-----------------

**General information**

Cable glands	metric	Diameter of sealing ring	50 mm
External thread	M 50 x 1.5	Halogen	No
Length of thread	18 mm	Material	Polyamide 6 (PA 6)
Operating temperature range, max.	100 °C	Operating temperature range, min.	-20 °C
Pitch of thread	1.5 mm	Protection degree	IP65, IP68 - 5 bar (30 min.)
Standards	in accordance with UL94 V-2	Tightening torque	8 Nm
UL 94 flammability rating	V-2		

**Classifications**

ETIM 6.0	EC000451	ETIM 7.0	EC000451
ETIM 8.0	EC000451	ETIM 9.0	EC000451
ECLASS 9.0	27-14-44-25	ECLASS 9.1	27-14-44-33
ECLASS 10.0	27-14-44-25	ECLASS 11.0	27-14-44-25
ECLASS 12.0	27-14-08-05	ECLASS 13.0	27-14-08-05
ECLASS 14.0	27-14-08-05		

**Environmental Product Compliance**

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--