

**IE-C5DE4UP0300PCSPCS-E****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**General ordering data**

|            |                                                                                                  |
|------------|--------------------------------------------------------------------------------------------------|
| Version    | Dragline cable, M8 P-code - IP67 straight pin, M8 P-code - IP67 straight pin, Cat. 5e, PUR, 30 m |
| Order No.  | <a href="#">2717780300</a>                                                                       |
| Type       | IE-C5DE4UP0300PCSPCS-E                                                                           |
| GTIN (EAN) | 4050118780345                                                                                    |
| Qty.       | 1 pc(s).                                                                                         |

**IE-C5DE4UP0300PCSPCS-E****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

|            |         |                 |                |
|------------|---------|-----------------|----------------|
| Length     | 30 m    | Length (inches) | 1,181.102 inch |
| Net weight | 1,851 g |                 |                |

**Temperatures**

|                       |                |
|-----------------------|----------------|
| Operating temperature | -40 °C...80 °C |
|-----------------------|----------------|

**Technical specifications for cable**

|                                |                                                      |                               |                             |
|--------------------------------|------------------------------------------------------|-------------------------------|-----------------------------|
| Bending cycles                 | 2 Mio                                                | Colour coding                 | white, yellow, blue, orange |
| Halogen                        | halogen-free, according to IEC 60754                 | Insulation                    | Polyolefin                  |
| Number of poles                | 4                                                    | Number of wires               | 4                           |
| Resistance to oils             | in accordance with IEC 60811:404                     | Resistance to spread of flame | Yes                         |
| Sheath material                | PUR                                                  | Sheathing colour              | black                       |
| Temperature range, moving      | -30...70 °C                                          | Temperature range, stationary | -40...80 °C                 |
| Test voltage: wire-wire-shield | 1 kV DC, 1 min, 1000 V <sub>eff</sub> , 50 Hz, 1 min |                               |                             |

**General technical data**

|                   |      |
|-------------------|------|
| Protection degree | IP67 |
|-------------------|------|

**Plug, left**

|           |                                                                    |
|-----------|--------------------------------------------------------------------|
| Plug left | M8, P-coded, IP67, male contact, straight, plug, Plastic, shielded |
|-----------|--------------------------------------------------------------------|

**Plug, right**

|            |                                                                    |
|------------|--------------------------------------------------------------------|
| Plug right | M8, P-coded, IP67, male contact, straight, plug, Plastic, shielded |
|------------|--------------------------------------------------------------------|

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002599    | ETIM 7.0    | EC002599    |
| ETIM 8.0    | EC002599    | ETIM 9.0    | EC002599    |
| ECLASS 9.0  | 27-06-03-08 | ECLASS 9.1  | 27-06-03-08 |
| ECLASS 10.0 | 27-06-03-08 | ECLASS 11.0 | 27-06-03-08 |
| ECLASS 12.0 | 27-06-03-08 | ECLASS 13.0 | 27-06-03-08 |

**Environmental Product Compliance**

|            |                |
|------------|----------------|
| REACH SVHC | Lead 7439-92-1 |
|------------|----------------|

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|            |                                          |
|------------|------------------------------------------|
| Catalogues | <a href="#">Catalogues in PDF-format</a> |
|------------|------------------------------------------|

Creation date June 14, 2024 6:07:36 AM CEST

Catalogue status 01.06.2024 / We reserve the right to make technical changes.

## IE-C5DE4UP0300PCSPCS-E

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

# Drawings

## Wiring

|     |        |     |
|-----|--------|-----|
| M12 |        | M12 |
| 1   | yellow | 1   |
| 2   | white  | 2   |
| 3   | orange | 3   |
| 4   | blue   | 4   |