

IE-C5DE4UP0030PCAPSA-E**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**General ordering data**

| | |
|------------|--|
| Version | Dragline cable, M8 P-code - IP67 angeled pin, M8 P-code - IP67 angeled socket, Cat. 5e, PUR, 3 m |
| Order No. | 2717810030 |
| Type | IE-C5DE4UP0030PCAPSA-E |
| GTIN (EAN) | 4050118779868 |
| Qty. | 1 pc(s). |

IE-C5DE4UP0030PCAPSA-E

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|-------|-----------------|-------------|
| Length | 3 m | Length (inches) | 118.11 inch |
| Net weight | 196 g | | |

Temperatures

| | |
|-----------------------|----------------|
| Operating temperature | -40 °C...80 °C |
|-----------------------|----------------|

Technical specifications for cable

| | | | |
|-------------------------------|--------------------------------------|--------------------------------|--|
| Bending cycles | 2 Mio | Colour coding | white, yellow, blue, orange |
| Halogen | halogen-free, according to IEC 60754 | Insulation | Polyolefin |
| Number of poles | 4 | Number of wires | 4 |
| Resistance to oils | in accordance with IEC 60811:404 | Resistance to spread of flame | Yes |
| Sheath material | PUR | Sheathing colour | black |
| Shielded | Yes | Temperature range, moving | -30...70 °C |
| Temperature range, stationary | -40...80 °C | Test voltage: wire-wire-shield | 1 kV DC, 1 min, 1000 V _{eff} , 50 Hz, 1 min |

General technical data

| | |
|-------------------|------|
| Protection degree | IP67 |
|-------------------|------|

Plug, left

| | |
|-----------|--|
| Plug left | M8, P-coded, IP67, male contact, angled 90°, plug, Plastic, shielded |
|-----------|--|

Plug, right

| | |
|------------|--|
| Plug right | M8, P-coded, IP67, female contact, angled 90°, plug, Plastic, shielded |
|------------|--|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC002599 | ETIM 7.0 | EC002599 |
| ETIM 8.0 | EC002599 | ETIM 9.0 | EC002599 |
| ECLASS 9.0 | 27-06-03-08 | ECLASS 9.1 | 27-06-03-08 |
| ECLASS 10.0 | 27-06-03-08 | ECLASS 11.0 | 27-06-03-08 |
| ECLASS 12.0 | 27-06-03-08 | ECLASS 13.0 | 27-06-03-08 |

Environmental Product Compliance

| | |
|------------|----------------|
| REACH SVHC | Lead 7439-92-1 |
|------------|----------------|

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------|--|
| Catalogues | Catalogues in PDF-format |
|------------|--|

Creation date July 4, 2024 10:51:16 PM CEST

Catalogue status 29.06.2024 / We reserve the right to make technical changes.

IE-C5DE4UP0030PCAPSA-E

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings

Wiring

| | | |
|-----|--------|-----|
| M12 | | M12 |
| 1 | yellow | 1 |
| 2 | white | 2 |
| 3 | orange | 3 |
| 4 | blue | 4 |