

SFM 1/24 1.2-1.8 MM WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

With the comprehensive MultiMark product family, you can achieve optimally structured and sustainable marking in every control cabinet. An example of this is our new SlimFix wire marker, which can be printed and snapped on particularly quickly. At the same time, they meet the highest requirements for vibration and shock resistance. The wire markers have an open design and can be easily and quickly installed before or after the wiring process.

General ordering data

| | |
|------------|---|
| Version | Conductor and cable markers, 1.2 - 1.8 mm, 24 x 3.8 mm, white |
| Order No. | 2719050000 |
| Type | SFM 1/24 1.2-1.8 MM WS |
| GTIN (EAN) | 4050118887785 |
| Qty. | 700 pc(s). |

SFM 1/24 1.2-1.8 MM WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

| | | | |
|------------|--------|-----------------|------------|
| Height | 24 mm | Height (inches) | 0.945 inch |
| Width | 3.8 mm | Width (inches) | 0.15 inch |
| Net weight | 0.4 g | | |

General data

| | | | |
|-----------------------------------|-------------|-----------------------------------|---------------|
| Colour | white | Halogen | No |
| Material | PC-ABS, TPU | Operating temperature range, max. | 90 °C |
| Operating temperature range, min. | -50 °C | Size of labelling field | 2.8 x 21.5 mm |
| Type of printing | neutral | UL 94 flammability rating | V-2 |
| Width | 3.8 mm | | |

Conductor and cable markers

| | | | |
|-------------------------------|----------------------|----------------------------------|-----------------------------|
| Conductor O.D. | 1.2 - 1.8 mm | Conductor O.D., max. | 1.8 mm |
| Conductor O.D., min. | 1.2 mm | Conductor cross-section, max. | 0.75 mm ² |
| Conductor cross-section, min. | 0.25 mm ² | Cross-section for connected wire | 0.25 - 0.75 mm ² |
| Halogen | No | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001530 | ETIM 7.0 | EC001530 |
| ETIM 8.0 | EC001530 | ETIM 9.0 | EC001530 |
| ECLASS 9.0 | 27-40-04-01 | ECLASS 9.1 | 27-40-04-01 |
| ECLASS 10.0 | 27-40-04-01 | ECLASS 11.0 | 27-28-11-02 |
| ECLASS 12.0 | 27-28-11-02 | ECLASS 13.0 | 27-28-11-02 |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| REACH SVHC | / |
| RoHS Compliance Status | Compliant without exemption |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------------|--|
| Engineering Data | CAD data – STEP |
| Catalogues | Catalogues in PDF-format |

SFM 1/24 1.2-1.8 MM WS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings




SFM 1/24 1.2-1.8 MM WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

THM MULTIMARK



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

| | |
|------------|----------------------------|
| Type | THM MMP ROLLER SFM 1 |
| Order No. | 2799000000 |
| GTIN (EAN) | 4064675259985 |
| Qty. | 1 pc(s). |