

IE-C6HD8UG0100A40XCS-E**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**General ordering data**

Version	Dragline cable, M12 X-type IP 67 straight male, RJ45 IP 20, Cat.6 _A / Class E _A (ISO/IEC 11801 2010), PUR, 10 m
Order No.	2723030100
Type	IE-C6HD8UG0100A40XCS-E
GTIN (EAN)	4050118785920
Qty.	1 pc(s).

IE-C6HD8UG0100A40XCS-E

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Length	10 m	Length (inches)	393.701 inch
Net weight	1,000 g		

Temperatures

Operating temperature	-40 °C...80 °C	Installation temperature	-30 °C...70 °C
-----------------------	----------------	--------------------------	----------------

Cable structure

Arrangement of wire cores	Twisted pair	Colour sequence or wires - wire pairs	white - blue, white - orange, white - green, white - brown
Complete shielding	Shielding braid made from copper wiring	Copper diameter	0.55 µm
Cross-section	4*2*AWG 26/19 - 4*2*0.128 mm ²	Insulation	PP
Insulation cross-section	0.98 mm	Material sheath	PUR
Number of wires	8	Sheath diameter, max.	7.8 mm
Sheathing colour	green (RAL 6018)	Shielding	S/FTP
Strands	19	Wire material	Stranded tin-plated copper wire
Wire pair shielding	Aluminium foil		

Electrical properties of cable

Category	Cat.6A / Class E _A (ISO/IEC 11801 2010)	Characteristic impedance	100 ± 15 Ω at 1–100 MHz
Loop resistance	280 Ω/km	Signal propagation time	5.34 ns/m
Test voltage: wire-wire-shield	700 V _{rms} , 50 Hz, 1 min	Transfer impedance	max. 30 mΩ/m at 10 MHz
Transmission rate	10 Gbit/s		

Mechanical and material properties of cable

Abrasion resistance	very good	Halogen	halogen-free
Min. bending radius, once only	4 x cable diameter	Min. bending radius, repetitive	7.5 x cable diameter
Pulling force	≤ 100 N	Resistance to oils	in accordance with IEC 60811-2-1; acc. to CSA 22.2, 4 days/100°C
Resistance to spread of flame	in accordance with IEC 60332-1-2, in accordance with UL 1581 VW-1 and CSA FT1	UV-resistant	Yes

Plug, left

Plug left	RJ45, IP20, male contact, straight, plug, Plastic, shielded
-----------	---

Plug, right

Plug right	M12, X-coded, IP67, male contact, straight, plug, Plastic, shielded
------------	---

IE-C6HD8UG0100A40XCS-E**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Classifications**

ETIM 6.0	EC002599	ETIM 7.0	EC002599
ETIM 8.0	EC002599	ETIM 9.0	EC002599
ECLASS 9.0	27-06-03-08	ECLASS 9.1	27-06-03-08
ECLASS 10.0	27-06-03-08	ECLASS 11.0	27-06-03-08
ECLASS 12.0	27-06-03-08	ECLASS 13.0	27-06-03-08

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--

IE-C6HD8UG0100A40XCS-E

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings**Connection diagram**

RJ45	1	White, Orange	1	M12
	2	Orange	2	
	3	White, Green	3	
	4	Blue	8	
	5	White, Blue	7	
	6	Green	4	
	7	White, Brown	5	
	8	Brown	6	

Printing