

KCMA-8-250-5A-1.5VA1**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Current transformers for retrofitting

Features:

- especially suitable for use in hard-to-reach places
- no cutting of the primary conductors necessary
- Unfolding of the current transformer without additional tools

General ordering data

Version	Primary current: 250 A, Secondary current max.: 5 A, Load: 1.5 VA, Tolerance class: 1, Split-core current transformer
Order No.	2728090000
Type	KCMA-8-250-5A-1.5VA1
GTIN (EAN)	4050118813685
Qty.	1 pc(s).
Manufacturer	MBS AG

Creation date July 16, 2024 10:08:29 PM CEST

Catalogue status 13.07.2024 / We reserve the right to make technical changes.

KCMA-8-250-5A-1.5VA1**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Net weight	1,431 g
------------	---------

Dimensions of live conductors

Type of conductor	Insulated conductor only	Round conductor	80 mm
Rail	80 x 120 mm		

Electrical attributes

Load	1.5 VA	Primary current	250 A
Secondary current	0...5 A	Tolerance class	1

Technical properties

Nominal frequency	50 Hz	Protection degree	IP20
-------------------	-------	-------------------	------

Insulation coordination

Tolerance class	1
-----------------	---

Classifications

ETIM 6.0	EC002048	ETIM 7.0	EC002048
ETIM 8.0	EC002048	ETIM 9.0	EC002048
ECLASS 9.0	27-21-09-02	ECLASS 9.1	27-21-09-02
ECLASS 10.0	27-21-09-02	ECLASS 11.0	27-21-09-02
ECLASS 12.0	27-21-09-02	ECLASS 13.0	27-21-09-02

Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

Approvals

ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	EU Declaration of Conformity
Catalogues	Catalogues in PDF-format

KCMA-8-250-5A-1.5VA1

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

