

BIT E6,3 1,2X6,5X70**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

1/4" hexagon drive to DIN 3126, form E6.3 for direct machine connection

Slot-head bits DIN 5264, 1/4" drive, E6.3 DIN 3126

General ordering data

| | |
|------------|---|
| Version | Screwdriver insert, Blade width (B): 6.5 mm, Blade length: 70 mm, Blade thickness (A): 1.2 mm |
| Order No. | 2748950000 |
| Type | BIT E6,3 1,2X6,5X70 |
| GTIN (EAN) | 4050118894820 |
| Qty. | 5 pc(s). |

BIT E6,3 1,2X6,5X70**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

| | | | |
|------------|-------|----------------|------------|
| Width | 70 mm | Width (inches) | 2.756 inch |
| Net weight | 12 g | | |

Technical data

| | |
|------------------------|--|
| Description of article | Bit with slotted blade 0.4 x 2.5 x 70 |
|------------------------|--|

Screwing tools

| | | | |
|-----------------|--------|---------------------|-------------------------|
| Blade length | 70 mm | Blade thickness (A) | 1.2 mm |
| Blade width (B) | 6.5 mm | Form | E 6.3 DIN 3126, Slotted |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC002116 | ETIM 7.0 | EC002116 |
| ETIM 8.0 | EC003864 | ETIM 9.0 | EC003864 |
| ECLASS 9.1 | 21-04-04-90 | ECLASS 10.0 | 21-04-04-90 |
| ECLASS 11.0 | 21-04-42-04 | ECLASS 12.0 | 21-04-42-04 |
| ECLASS 13.0 | 21-04-42-04 | | |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------|--|
| Catalogues | Catalogues in PDF-format |
|------------|--|