

SDIS SLIM 1.0X5.5X125**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

VDE insulated screwdriver sets, for working on live parts up to 1000 V AC and 1500 V DC, DIN EN 60900. IEC 900. Each piece is "GS" safety tested. Blade made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, gun-metal finish.

General ordering data

Version	Mounting tool, Blade width (B): 5.5 mm, Blade length: 125 mm, Blade thickness (A): 1 mm
Order No.	2749630000
Type	SDIS SLIM 1.0X5.5X125
GTIN (EAN)	4050118896374
Qty.	1 pc(s).

SDIS SLIM 1.0X5.5X125**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Length	240 mm	Length (inches)	9.449 inch
Net weight	80 g		

Technical data

Description of article	VDE-insulated screw-driver with slotted blade 1.0x5.5x125, SlimLine	Version	straight
------------------------	--	---------	----------

Screwing tools

Blade length	125 mm	Blade thickness (A)	1 mm
Blade width (B)	5.5 mm	Form	Slotted

Classifications

ETIM 6.0	EC000158	ETIM 7.0	EC000158
ETIM 8.0	EC000158	ETIM 9.0	EC000158
ECLASS 9.0	21-04-04-07	ECLASS 9.1	21-04-04-07
ECLASS 10.0	21-04-04-07	ECLASS 11.0	21-04-04-07
ECLASS 12.0	21-04-04-07	ECLASS 13.0	21-04-04-07

Downloads

Catalogues	Catalogues in PDF-format
------------	--