

**SDIK SLIM PH2 X 100****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

VDE insulated screwdriver sets, for working on live parts up to 1000 V AC and 1500 V DC, DIN EN 60900. IEC 900. Each piece is "GS" safety tested. Blade made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, gun-metal finish.

**General ordering data**

Version	Screwdriver, Blade width (B): 2 mm, 100 mm, Blade thickness (A): 2
Order No.	<a href="#">2749660000</a>
Type	SDIK SLIM PH2 X 100
GTIN (EAN)	4050118896404
Qty.	1 pc(s).

**SDIK SLIM PH2 X 100****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Width	215 mm	Width (inches)	8.465 inch
Net weight	90 g		

**Technical data**

Description of article	VDE-insulated crosshead screwdriver, Phillips size 2, SlimLine	Version	straight
------------------------	--	---------	----------

**Screwing tools**

Blade length	100 mm	Blade size, crosshead	2
Blade width (B)	2 mm	Form	Crosshead, round
Size	2		

**Classifications**

ETIM 6.0	EC000144	ETIM 7.0	EC000144
ETIM 8.0	EC000144	ETIM 9.0	EC000144
ECLASS 9.0	21-04-04-06	ECLASS 9.1	21-04-04-06
ECLASS 10.0	21-04-04-06	ECLASS 11.0	21-04-04-06
ECLASS 12.0	21-04-04-06	ECLASS 13.0	21-04-04-06

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--