

SDIS 0.8X4.0X100**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

VDE insulated slot-head screwdriver, SDI DIN 7437, ISO 2380/2, drive output acc. to DIN 5264, ISO 2380/1. SoftFinish grip

General ordering data

Version	Screwdriver, Blade width (B): 4 mm, Blade length: 100 mm, Blade thickness (A): 0.8 mm
Order No.	2749820000
Type	SDIS 0.8X4.0X100
GTIN (EAN)	4050118897029
Qty.	1 pc(s).

SDIS 0.8X4.0X100**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Length	205 mm	Length (inches)	8.071 inch
Net weight	45 g		

Technical data

Description of article	VDE-insulated screw-driver with slotted blade 0.8x4.0x100	Version	straight
------------------------	--------------------------------------------------------------	---------	----------

Screwing tools

Blade length	100 mm	Blade thickness (A)	0.8 mm
Blade type	B	Blade width (B)	4 mm
Form	Slotted		

Classifications

ETIM 6.0	EC000158	ETIM 7.0	EC000158
ETIM 8.0	EC000158	ETIM 9.0	EC000158
ECLASS 9.0	21-04-04-07	ECLASS 9.1	21-04-04-07
ECLASS 10.0	21-04-04-07	ECLASS 11.0	21-04-04-07
ECLASS 12.0	21-04-04-07	ECLASS 13.0	21-04-04-07

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	b28ab223-64ec-44cf-adb0-4dd6ebcae141

Downloads

Catalogues	Catalogues in PDF-format
------------	------------------------------------------