

**SDIS 1.0X4.5X125****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

VDE insulated slot-head screwdriver, SDI DIN 7437, ISO 2380/2, drive output acc. to DIN 5264, ISO 2380/1. SoftFinish grip

**General ordering data**

Version	Screwdriver, Blade width (B): 4.5 mm, Blade length: 125 mm, Blade thickness (A): 1 mm
Order No.	<a href="#">2749830000</a>
Type	SDIS 1.0X4.5X125
GTIN (EAN)	4050118897036
Qty.	1 pc(s).

**SDIS 1.0X4.5X125****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Length	230 mm	Length (inches)	9.055 inch
Net weight	110 g		

**Technical data**

Description of article	VDE-insulated screw-driver with slotted blade 1.0x4.5x125	Version	straight
------------------------	--	---------	----------

**Screwing tools**

Blade length	125 mm	Blade thickness (A)	1 mm
Blade type	B	Blade width (B)	4.5 mm
Form	Slotted		

**Classifications**

ETIM 6.0	EC000158	ETIM 7.0	EC000158
ETIM 8.0	EC000158	ETIM 9.0	EC000158
ECLASS 9.0	21-04-04-07	ECLASS 9.1	21-04-04-07
ECLASS 10.0	21-04-04-07	ECLASS 11.0	21-04-04-07
ECLASS 12.0	21-04-04-07	ECLASS 13.0	21-04-04-07
ECLASS 14.0	21-04-04-07		

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	b28ab223-64ec-44cf-adb0-4dd6ebcae141
RoHS Compliance Status	Not affected

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--