

SDIS 1.2X6.5X150**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

VDE insulated slot-head screwdriver, SDI DIN 7437, ISO 2380/2, drive output acc. to DIN 5264, ISO 2380/1. SoftFinish grip

General ordering data

| | |
|------------|---|
| Version | Screwdriver, Blade width (B): 6.5 mm, Blade length: 150 mm, Blade thickness (A): 1.2 mm |
| Order No. | 2749860000 |
| Type | SDIS 1.2X6.5X150 |
| GTIN (EAN) | 4050118897067 |
| Qty. | 1 pc(s). |

SDIS 1.2X6.5X150**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

| | | | |
|------------|--------|-----------------|-------------|
| Length | 265 mm | Length (inches) | 10.433 inch |
| Net weight | 113 g | | |

Technical data

| | | | |
|------------------------|--|---------|----------|
| Description of article | VDE-insulated screw-driver with slotted blade 1.2x6.5x150 | Version | straight |
|------------------------|--|---------|----------|

Screwing tools

| | | | |
|--------------|---------|---------------------|--------|
| Blade length | 150 mm | Blade thickness (A) | 1.2 mm |
| Blade type | B | Blade width (B) | 6.5 mm |
| Form | Slotted | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000158 | ETIM 7.0 | EC000158 |
| ETIM 8.0 | EC000158 | ETIM 9.0 | EC000158 |
| ECLASS 9.0 | 21-04-04-07 | ECLASS 9.1 | 21-04-04-07 |
| ECLASS 10.0 | 21-04-04-07 | ECLASS 11.0 | 21-04-04-07 |
| ECLASS 12.0 | 21-04-04-07 | ECLASS 13.0 | 21-04-04-07 |

Downloads

| | |
|------------|--|
| Catalogues | Catalogues in PDF-format |
|------------|--|