

SDIS 1.2X8.0X175**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

VDE insulated slot-head screwdriver, SDI DIN 7437, ISO 2380/2, drive output acc. to DIN 5264, ISO 2380/1. SoftFinish grip

General ordering data

Version	Screwdriver, Blade width (B): 8 mm, Blade length: 175 mm, Blade thickness (A): 1.6 mm
Order No.	2749870000
Type	SDIS 1.2X8.0X175
GTIN (EAN)	4050118897074
Qty.	1 pc(s).

SDIS 1.2X8.0X175**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Length	290 mm	Length (inches)	11.417 inch
Net weight	180 g		

Technical data

Description of article	VDE-insulated screw-driver with slotted blade 1.6x8.0x175	Version	straight
------------------------	--------------------------------------------------------------	---------	----------

Screwing tools

Blade length	175 mm	Blade thickness (A)	1.6 mm
Blade type	B	Blade width (B)	8 mm
Form	Slotted		

Classifications

ETIM 6.0	EC000158	ETIM 7.0	EC000158
ETIM 8.0	EC000158	ETIM 9.0	EC000158
ECLASS 9.0	21-04-04-07	ECLASS 9.1	21-04-04-07
ECLASS 10.0	21-04-04-07	ECLASS 11.0	21-04-04-07
ECLASS 12.0	21-04-04-07	ECLASS 13.0	21-04-04-07
ECLASS 14.0	21-04-04-07		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	No SVHC above 0.1 wt%

Downloads

Catalogues	Catalogues in PDF-format
------------	------------------------------------------