

**SDIK PH3 X 150****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com) 1000 V  
IEC 60900

VDE insulated crosshead screwdriver, for Phillips screws,  
SDIK PH DIN 7438, ISO 8764/2-PH, output to ISO 8764-  
PH, SoftFinish grip

**General ordering data**

Version	Screwdriver, Blade width (B): 3 mm, 150 mm, Blade thickness (A): 3
Order No.	<a href="#">2749910000</a>
Type	SDIK PH3 X 150
GTIN (EAN)	4050118897210
Qty.	1 pc(s).

**SDIK PH3 X 150****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Width	270 mm	Width (inches)	10.63 inch
Net weight	141 g		

**Technical data**

Description of article	VDE-insulated crosshead screwdriver, Phillips size 3	Version	straight
------------------------	--	---------	----------

**Screwing tools**

Blade length	150 mm	Blade size, crosshead	3
Blade width (B)	3 mm	Form	Philips, round
Size	3		

**Classifications**

ETIM 6.0	EC000144	ETIM 7.0	EC000144
ETIM 8.0	EC000144	ETIM 9.0	EC000144
ECLASS 9.0	21-04-04-06	ECLASS 9.1	21-04-04-06
ECLASS 10.0	21-04-04-06	ECLASS 11.0	21-04-04-06
ECLASS 12.0	21-04-04-06	ECLASS 13.0	21-04-04-06

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	b28ab223-64ec-44cf-adb0-4dd6ebcae141

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--